

Handheld Temperature Probes

NiCr-Ni

Surface Probe



Description	Temperature-range	N-Length [mm]	Diam. [mm]	T90	Art.-No.
Very quick probe, especially for rifts	-50... +400°C	160		2	0600 1083
With spring loaded Cu plate for steady pressure	-50... +650°C	130	4	12	0600 1001
Robust Immersion probe	-50... +1100°C	130	3	8	0600 1002