

3.3V HCMOS/ TTL COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR

ASFL1



RoHS
Compliant



5.0 x 3.2 x 1.3mm

FEATURES:

- Tri state function
- Suitable for high density SMT
- Available tight stability option +/-20ppm
- Seam sealed package assures high reliability performance
- Suitable for RoHS compliant reflow process

APPLICATIONS:

- CCD clock for VTR camera
- Equipment connected to PC or PC cards
- Thin equipment
- Wireless communication
- PDA, Laptop computer

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		0.321	-----	133.33	MHz	
Operating Temperature		-10	-----	+70	°C	See options
Storage Temperature		-55	-----	+125	°C	
Overall Frequency Stability		-100	-----	+100	ppm	See options
Supply Voltage (Vdd)		2.97	3.3	3.63	V	
Input Current	0.321MHz ~ 29.9MHz	-----	8	15	mA	
	30MHz ~ 79.9MHz	-----	20	45		
	80MHz ~ 133.33MHz	-----	28	85		
Symmetry (@ 1/2Vdd)		40	50	60	%	See options
Rise and Fall Time (Tr/Tf)	0.321MHz ~ 29.9MHz	-----	5	10	ns	
	30MHz ~ 79.9MHz	-----	5	7		
	80MHz ~ 133.33MHz	-----	3	7		
Output Load		-----	-----	15	pF	
		-----	-----	5	TTL	
Output Voltage	VOH	0.9*Vdd	-----	-----	V	
	VOL	-----	-----	0.1*Vdd	V	
Tri-state Function	VIH	0.7*Vdd	-----	-----	V	"1" or Open: Oscillation
	VIL	-----	-----	0.3*Vdd	V	"0": Output disable (Hi Z)
Disable Current				10	µA	
Start-up Time	0.321MHz ~ 29.9MHz	-----	1	10	ms	
	30MHz ~ 79.9MHz	-----	3	10		
	80MHz ~ 133.33MHz	-----	3	10		
Phase Jitter RMS (12kHz to 20MHz)		-----	-----	1	ps	Reference only. Please contact Abracon for specific frequencies
Aging		-5.0	-----	+5.0	ppm	@+25°C First year

OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ASFL1- MHz - -

Frequency in MHz
e.g. 24.576MHz
14.31818MHz
26.000MHz

Operating Temp.
I: 0°C ~ +50°C
D: -10°C ~ +60°C
E: -20°C ~ +70°C
F: -30°C ~ +70°C
N: -30°C ~ +85°C
L: -40°C ~ +85°C

Freq. Stability
J: ± 20 ppm(*)
R: ± 25 ppm
K: ± 30 ppm
H: ± 35 ppm
B: ± 40ppm
C: ± 50 ppm

Symmetry
Blank: 40/60% @1/2Vdd
S: 45/55% @1/2Vdd

(*) Temp option I, D, E and
-10°C ~ +70°C only.

Packaging
Blank: Bulk
T: 1000pcs/reel
T2: 250pcs/reel

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 04.13.11**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

3.3V HCMOS /TTL COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR

ASFL1



RoHS
Compliant



5.0 x 3.2 x 1.3mm

OUTLINE DRAWING:



Recommended land pattern



Pin	Function
1	Tri-State
2	GND
3	Output
4	Vdd

Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

Dimensions: inches (mm)

TAPE & REEL:

T= Tape and reel (1,000pcs/reel)
T2= Tape and reel (250pcs/reel)

Dimensions: mm



REFLOW PROFILE:



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 04.13.11**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com