

LED BA 9s (MBC/MCC) superbright, red, 24 V**1.90.690.341/0000****Electrical characteristics of LED**

Max. current, I_F	15 mA
LED wavelength typ.	621
Forward voltage typ. U_F at I_F	24
LED breakdown voltage U_R bei I_F	24
Light intensity	250

Other specifications

Socket	BA 9 s
Color	red
Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+65 °C
ROHS compliant	yes
REACH compliant	yes