

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.




LOC
HDIST
-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	FIRST ISSUE	22AUG2007	JV	RL

NOTES:

- ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED ON THE CONTAINER WITH THE FOLLOWING INFORMATION: PART NUMBER & DATE CODE OF MFR.
- MATERIALS:
SOCKET BODY: TeCu
CROWN CONTACT: BeCu
HOUSING: THERMOPLASTIC, 94V-0, COLOR PER TABLE
- FINISHES:
SOCKET BODY: SILVER PLATING: MIN. 5µm
OVER MIN. 1µm NICKEL.
CROWN CONTACT: GOLD PLATING: MIN. 0.75µm
OVER MIN. 1µm NICKEL.
- △4 ROTATION ARC.
- FOR TERMINATION REFER TO 1926079-1
- MAXIMUM CABLE DIAMETER NOT TO EXCEED 1/2"



6648234-3	BLUE
6648234-2	RED
6648234-1	BLACK



SCALE 1:1

3	CROWN, CONTACT, SIZE #0	1
2	HOUSING, CROWN SOCKET, SIZE #2	1
1	CONTACT SOCKET BODY, RIGHT ANGLE, SIZE #0	1
ITEM NO.	DESCRIPTION	QUANT.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0,2 1 PLC ±0,1 2 PLC ±0,05 3 PLC ±0,025 4 PLC ±0,005 ANGLES ±2°
MATERIAL -	FINISH -

DWN	J. VOS	23-Aug-07
CHK	R. LOKKER	23-Aug-07
APVD	J. BROEKSTEEG	23-Aug-07
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
NAME JUMPER, CROWN SOCKET, PIN SIZE #0 WITH #0 AWG CRIMP BARREL	
SIZE A3	CAGE CODE 00779
DRAWING NO C-6648234	RESTRICTED TO -
SCALE 2:1	SHEET 1 OF 1
REV B	