


EM-DUO 120/15

Order No.: 5600461

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=5600461>

Rail-mountable double socket, for mounting on 35 mm DIN rail in acc. with EN 60715, housing color: white, with screw connection, national version: USA



Commercial data

EAN	4017918929930
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.2463 KG
Catalog page information	Page 603 (IF-2009)

<http://>www.download.phoenixcontact.com

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	120 V AC
Nominal current I_N	15 A
For country-specific use in	USA
Color	white
Insulating material	PVC 94 V0
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Standards/regulations	UL 508

Width	83 mm
Height	49 mm
Depth	134 mm

Connection data

Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	6 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	4 mm²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3


Certificates / Approvals




Certification CUL Listed, UL Listed

Diagrams/Drawings


Connection diagram



Dimensioned drawing



Circuit diagram



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;