


MATERIAL

Insulator : NY66 94V-2

Contact Pin : Phorphos bronze

SPECIFICATION

Current Rate : 3 amperes MAX

Insulation Resistance :1000 megohms MAX

Contact Resistance : 30mΩMax. at DC 100mA

Dielectric Voltage :AC 650 volts RMS at sea leve

Operation Temperature : -55°C to +105°C

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准	SCALE 比例 参考	TOLERANCE 容許公差 .0 =±.30 .00 =±.20 .000 =±.00X .0000=± ANG.=±3°	PART NAME 品名 2.0mm MINI JUMPER 2P H:10.9mm OPEN TYPE GOLD PLATING BLACK COLOR ROHS LOW-LEAD
DWG. 製圖 Hedy	UNIT 單位 MM	SIZE. 紙張尺寸 A 4	PART NO. 料號 C9700-02EAGB00R
DATE 制表日 2010/04/22	PAGE 張數 1 / 1	REV. 版次 A	