







SEAL/MYLAR ASSEMBLY DETAIL
NO SCALE
TYPE 101

- NOTES
1. THE MYLAR TAPE IS ONLY A CARRIER USED AS A PROCESS AID AND IS NOT PART OF THE FINAL HARNESS ASSEMBLY.
 2. WHEN PARTS ARE SHIPPED, THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINER MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.



SEAL/MYLAR ASSEMBLY DETAIL
NO SCALE
TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

- NOTES
1. THE MYLAR TAPE IS ONLY A CARRIER USED AS A PROCESS AID AND IS NOT PART OF THE FINAL HARNESS ASSEMBLY.
 2. WHEN PARTS ARE SHIPPED, THEY MUST BE PACKED IN PLASTIC BAGS OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS. BAGS OR LINER MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.



GT 150 3.5 CL (3.2 X 4.0 OVAL INTERNAL CAVITY DIAMETER)

CABLE SEAL	REV	N/P	STATUS	USAGE	REPLACED BY	TYPE	MAT'L SPEC	ALTERNATE MATERIAL SPEC	MATERIAL DESCRIPTION	COLOR	CABLE O.D. RANGE	$\phi C \pm 0.1$	E	$\phi G \pm 0.1$	VOL (CM ³)	MYLAR & CABLE SEAL ASM	REV	N/P	STATUS	MYLAR STRIP	TYPE
15473821	01	AE	OBSOLETE	-	-	102	M3469007	-	SILICONE, 50 SHORE, 2% OIL	GREEN	2.00-2.20	2.4	3.25	3.9 +0.1/-0.05	0.029	-	-	-	-	-	-
15366022	01	AL	-	-	-	101	M3469007	M4361007	SILICONE, 50 SHORE, 2% OIL	GREEN	1.40-1.90	2.4	3.2	4 +0.1/-0.05	0.034	-	-	-	-	-	-
15305351	02	AK	-	-	-	101	M3469006	M4361006	SILICONE, 50 SHORE, 2% OIL	YELLOW	1.70-2.10	2.4	3.25	3.9	0.033	12191155	A1	OBSOLETE	R0072686	-	-
12191223	04	AF	-	RESTRICTED	15366022	101	M2261001	M2261001	SILICONE, 50 SHORE, 4% OIL	GRAY	1.40-1.90	2.4	3.25	4 +0.1/-0.05	0.034	12191155	D3	AF	-	-	102

GT 150 (4.0 INTERNAL CAVITY DIAMETER)

15366060	02	AB	-	-	-	102	M3469008	M4361008	SILICONE, 50 SHORE, 2% OIL	BLUE	1.86-2.40	2.8	3.5	4.5	0.037	-	-	-	-	-	-
15366021	01	AL	-	-	-	101	M3469011	M4361011	SILICONE, 50 SHORE, 2% OIL	WHITE	1.20-1.90	2.8	3.5	4.5	0.041	-	-	-	-	-	-
13667445	01	AA	-	-	-	101	M3466011	-	SILICONE, 50 SHORE, 1% OIL	WHITE	1.20-1.90	2.8	3.5	4.5	0.041	-	-	-	-	-	-
12191227	04	AB	-	RESTRICTED	15366060	102	M3471008	M2261008	SILICONE, 50 SHORE, 4% OIL	BLUE	1.86-2.40	2.8	3.5	4.5	0.037	12191153	B8	-	-	M5235002	102
12191226	D10	-	-	RESTRICTED	15366021	101	M3471011	M2261011	SILICONE, 50 SHORE, 4% OIL	WHITE	1.20-1.90	2.8	3.5	4.5	0.041	12191152	B9	-	-	M5235002	102
CABLE SEAL	REV	N/P	STATUS	USAGE	REPLACED BY	TYPE	MAT'L SPEC	ALTERNATE MATERIAL SPEC	MATERIAL DESCRIPTION	COLOR	CABLE O.D. RANGE	$\phi C \pm 0.1$	E	$\phi G \pm 0.1$	VOL (CM ³)	MYLAR & CABLE SEAL ASM	REV	N/P	STATUS	MYLAR STRIP	TYPE

GT 280 (5.2 INTERNAL CAVITY DIAMETER)

15366064	01	AK	-	-	-	101	M3469039	M4361009	SILICONE, 50 SHORE, 2% OIL	PURPLE	1.86-2.40	3.45	3.5	5.75	0.067	-	-	-	-	-	-
15366063	01	AJ	-	-	-	101	M3469003	M4361012	SILICONE, 50 SHORE, 2% OIL	GRAY	1.20-1.90	3.45	3.5	5.75	0.073	-	-	-	-	-	-
15366061	01	AJ	-	-	-	101	M3469037	M4361019	SILICONE, 50 SHORE, 2% OIL	DARK RED	2.09-2.66	3.45	3.5	5.75	0.063	-	-	-	-	-	-
15366674	02	AL	-	-	-	103	M3469008	M4361008	SILICONE, 50 SHORE, 2% OIL	BLUE	2.70-3.20	3.6	4.0 15	3.5	5.75 40.15	0.056	-	-	-	-	-
12191231	B11	-	-	RESTRICTED	15366064	101	M3471039	M2261009	SILICONE, 50 SHORE, 4% OIL	PURPLE	1.86-2.40	3.45	3.5	5.75	0.067	12191157	B6	-	-	M5235004	101
12191230	C9	-	-	RESTRICTED	15366063	101	M3471033	M2261012	SILICONE, 50 SHORE, 4% OIL	GRAY	1.20-1.90	3.45	3.5	5.75	0.073	12191156	B6	-	-	M5235004	101
12191228	B10	-	-	RESTRICTED	15366061	101	M3471037	M2261019	SILICONE, 50 SHORE, 4% OIL	DARK RED	2.09-2.66	3.45	3.5	5.75	0.063	12191154	B6	-	-	M5235004	101
CABLE SEAL	REV	N/P	STATUS	USAGE	REPLACED BY	TYPE	MAT'L SPEC	ALTERNATE MAT'L SPEC	MATERIAL DESCRIPTION	COLOR	CABLE O.D. RANGE	$\phi C \pm 0.1$	E	$\phi G \pm 0.1$	VOL (CM ³)	MYLAR & CABLE SEAL	REV	N/P	STATUS	MYLAR STRIP	TYPE


GT 280 (5.8 INTERNAL CAVITY DIAMETER)

13601285	01	-	-	RESTRICTED	-	101	M5122005	-	FLUOROSILICONE, 40 SHORE	ORANGE	1.20-1.90	4.25	3.5	6.35	0.102	-	-	-	-	-	-
13601284	01	-	-	RESTRICTED	-	101	M5122008	-	FLUOROSILICONE, 40 SHORE	BLUE	1.86-2.40	4.25	3.5	6.35	0.096	-	-	-	-	-	-
13605251	02	-	-	RESTRICTED	-	101	M4358005	-	FLUOROSILICONE, 40 SHORE	ORANGE	1.20-1.90	4.25	3.5	6.35	0.102	-	-	-	-	-	-
13649970	02	-	-	RESTRICTED	-	101	M4358008	-	FLUOROSILICONE, 40 SHORE	BLUE	1.86-2.40	4.25	3.5	6.35	0.096	-	-	-	-	-	-
15366067	01	AM	-	-	-	101	M3469038	M4361029	SILICONE, 50 SHORE, 2% OIL	TAN	2.50-3.20	4.25	3.5	6.35	0.085	-	-	-	-	-	-
15366066	01	AK	-	-	-	101	M3469006	M4361006	SILICONE, 50 SHORE, 2% OIL	YELLOW	1.86-2.40	4.25	3.5	6.35	0.096	-	-	-	-	-	-
15366065	01	AL	-	-	-	101	M3469005	M4361005	SILICONE, 50 SHORE, 2% OIL	ORANGE	1.20-1.90	4.25	3.5	6.35	0.102	-	-	-	-	-	-
12191235	D1	AK	-	-	-	101	M3469039	M4361029	SILICONE, 50 SHORE, 2% OIL	PURPLE	3.40-3.90	4.25	3.5	6.35	0.063	12191224	B1	-	OBSOLETE	R0065622	-
12191234	D6	-	-	RESTRICTED	15366067	101	M3471038	M2261029	SILICONE, 50 SHORE, 4% OIL	TAN	2.50-3.20	4.25	3.5	6.35	0.085	12191223	D9	-	-	M5235003	101
12191233	B10	-	-	RESTRICTED	15366066	101	M3471006	M2261006	SILICONE, 50 SHORE, 4% OIL	YELLOW	1.86-2.40	4.25	3.5	6.35	0.096	12191222	B9	-	-	M5235003	101
12191232	C9	-	-	RESTRICTED	15366065	101	M3471005	M2261005	SILICONE, 50 SHORE, 4% OIL	ORANGE	1.20-1.90	4.25	3.5	6.35	0.102	12191221	B9	-	-	M5235003	101
CABLE SEAL	REV	N/P	STATUS	USAGE	REPL. BY	TYPE	MAT'L SPEC	ALTERNATE MATERIAL SPEC	MATERIAL DESCRIPTION	COLOR	CABLE O.D. RANGE	$\phi C \pm 0.1$	E	$\phi G \pm 0.1$	VOL (CM ³)	MYLAR & CABLE SEAL ASM	REV	N/P	STATUS	MYLAR STRIP	TYPE

12191225
1 OF 1
12191225

SYMBOL DEFINITION	MISSING SYMBOLS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	1 3-4 6 9
TOTAL NO OF INSPECTIONS REQUIRED	4
LAST NO. USED	9

DATE	SYMBOL	REV	N/P	ZONE	REVISION HISTORY	AUTH	GR	APPROV
07ED3	-	06	-	-	12191152 THRU 12191157 & 12191221 THRU 12191223 - REVISED TOOL QUALIFICATION DRAWING	239238	J5	J5
11AP03	-	07	-	-	12191221, 12191222, 12191223 - CHANGED MYLAR STRIP MATERIAL - SEE TOO	239244	SS	SS
19FE04	R	08	-	-	12191221, 23 & 1219152-57 - UPDATED FROM ATTRIBUTES: 12191223-34 - UPDATED MAT'L SPEC: ALL ACTIVE PARTS - REMOVED LABEL	251754	MDH	JAA
09MR04	R	09	-	-	12191221, 23 - CORRECTED REVISION LEVELS OR DRAWINGS	252831	LMB	LMB
30MR04	R	10	-	-	ADDED CUSTOMER SPECIFIC DRAWING	253027	MUM	MUM
02JL04	R	11	-	-	12191222, 12191223, 12191223 - CORRECTED BSL	256636	JLL	JLL
23FE05	R	12	-	-	ALL ACTIVE PARTS - ADDED RESTRICTED STATUS, ALTERNATE MAT'L SPEC. SEE NOTE 3 TO CABLE O.D. DIA AND DIM "C"	265082	RR	RR
24AUG05	R	13	-	-	ALL PARTS - REVISED CHART: 12191227 - REVISED INTERNAL NECK GROOVE, ADDED MYLAR/SEAL ASSEMBLY DETAIL	270772	PCP	PCP
19W06	R	14	-	-	ALL ACTIVE PARTS - REMOVED DIMS 44 & 46 FROM DRG AND DIM #7 "17" FROM CHART	280824	AB	BRO
08JAN07	R	15	-	-	ADDED 13649970, 13650517 AND RELEASED, ALL ACTIVE PARTS - REVISED CHART	401495	PCP	PCP
03DEC07	R	16	-	-	12191235, 13647449, 13395751, 13336674, 13366021, 13366061, 13366063, 13366065, 13366067 & 13473821 - MOVED ON SHIT 02: ALL PARTS - UPDATED CHART INFO AND SHEET 1 OF 1 WAS SHEET 1 OF 21 13473821 - OBSOLETE	402049	JBD	JAA
04DEC07	R	17	-	-	13641024 & 13641025 - RELEASED: 13649970 - RESTRICTED, CABLE O.D. WAS 2.09-2.66, Ø C WAS 3.45 & Ø B WAS 5.75: 13650517 - RESTRICTED, Ø C WAS 3.45 AND Ø B WAS 5.75	403110	JBD	JAA



TYPE 103
SAME AS TYPE 101 EXCEPT AS
SHOWN AND AS NOTED IN CHART



TYPE 104



TYPE 105



TYPE 106



TYPE 107



TYPE 108



TYPE 109




TYPE 110




TYPE 111




TYPE 112




TYPE 113



TYPE 114



TYPE 115



TYPE 116

TYPE 117

TYPE 118

TYPE 119

TYPE 120

TYPE 121

TYPE 122

TYPE 123</

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12191221](#) [12191222](#)