


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	750 kcmil
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-15/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BLACK
Panduit Die Index No. on Barrel	P106
Alternate Industry Die Index No. () on Barrel	(24)



LISTED
Wire Connector



								
04	9/13	JHNU	JHNU	REVISED THICKNESS TO .29, WIDTH TO 1.34	N10885ER-LCDN750-38D-CUST	RGB	RGB	LCDN750-38D-6 Copper Lug - Narrow Tongue, Two-Hole, Standard Barrel
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCDN750-38D-CUST