





Product Bulletin Number SA-SSCB15 6/2007

- Provides permanent identification of pipes, conduit, valves, cables and equipment in harsh environments
- Designed for use with **PANDUIT® PAN-STEEL®** Stainless Steel Cable Ties for fast installation at lowest installed cost
- All marker plates can be embossed or laser etched with **PANDUIT** Factory Custom Marking Service
- For on-site custom marking use the metal indenting machine

	Part Number	Material	Color	Length/ Diameter		Width		Custom Marking Parameters*			Thickness		Std. Pkg. Qty.
				In.	mm	In.	mm	Max. 3/16" (4.77mm) Character Per Line	Max. Lines of Text	Used with PAN-STEEL® Cable Ties**	In.	mm	
 MMP350-C	MMP350-C*	304 Stainless Steel	Natural	3.50	89	.75	19	23	3	MLT-S	.010	.25	100
	MMP350-C316*	316 Stainless Steel											100
 MMP350H-C	MMP350H-C*	304 Stainless Steel	Natural	3.50	89	.75	19	20	3	MLT-H	.010	.25	100
	MMP350H-C316*	316 Stainless Steel											100
 MMP350DB-C	MMP350DB-C*	304 Stainless Steel	Natural	3.50	89	1.12	29	20	3	MLT-H	.015	.38	100
	MMP350DB-C316*	316 Stainless Steel											100
 MMP350W38-C	MMP350W38-C*	304 Stainless Steel	Natural	3.50	89	.38	10	23	1	MLT-S	.010	.25	100
	MMP350W38-C316*	316 Stainless Steel											100
 MMP172-C	MMP172-C*	304 Stainless Steel	Natural	1.72	44	.75	19	8	3	MLT-S	.010	.25	100
	MMP172-C316*	316 Stainless Steel											100
 MMP172W38-C	MMP172W38-C*	304 Stainless Steel	Natural	1.72	44	.38	10	8	1	MLT-S	.010	.25	100
	MMP172W38-C316*	316 Stainless Steel											100
 MMP350W17-Q	MMP350W17-Q	304 Stainless Steel	Natural	3.50	89	1.73	44	26	6	MLT-S	.015	.38	25
 MMP338W21-Q	MMP338W21-Q	304 Stainless Steel	Natural	3.38	86	2.13	54	22	6	MLT-S	.015	.38	25
*See last page for PANDUIT Factory Custom Marking Service Information.													
	MT350-C	304 Stainless Steel	Natural	3.50	89	.75	19	26	3	MLT-S	.010	.25	100
 MT350-C	MT350-C316	316 Stainless Steel											100
	MT172-C	304 Stainless Steel	Natural	1.72	44	.75	19	10	3	MLT-S	.010	.25	100
 MT172-C	MT172-C316	316 Stainless Steel											100



MTB1D-Q



MTB150D-Q



MTB213D-Q



MT125S-Q

MT1D-Q	304 Stainless Steel	Natural										25
MT1D-Q316	316 Stainless Steel		1.00	25	—	—	5	1	MLT-S	.035	.89	25
MTB1D-Q	Brass	Brass								.040	1.02	25
MT150D-Q	304 Stainless Steel	Natural										25
MT150D-Q316	316 Stainless Steel		1.50	38	—	—	5, 6, 5	3	MLT-S	.035	.89	25
MTB150D-Q	Brass	Brass								.040	1.02	25
MT213D-Q	304 Stainless Steel	Natural										25
MT213D-Q316	316 Stainless Steel		2.13	54	—	—	6, 12, 8	3	MLT-S	.015	.38	25
MTB213D-Q	Brass	Brass										25
MT125S-Q	304 Stainless Steel	Natural	1.25	32	1.25	32	5	2	MLT-S	.035	.89	25

*See last page for *PANDUIT* Factory Custom Marking Service Information.

**See page 5 for *PAN-Steel*® Stainless Steel Cable Ties.

^Order number of pieces required, in multiples of Standard Package Quantity.