







(c) NOTES:

1. METALSHELLS: COPPER ALLOY;
min. 315µin TIN over 40-80µin NICKEL
2. INSULATOR: TPE
3. CLAMPS: STAINLESS STEEL
4. SCREW: STAINLESS STEEL

- (d) 5. CONNECTOR IS PART MARKED: **PART NO. CONEC ABC**

No. of pos.	A _{-0,76}	B _{+0,25}	C	D _{-0,3}	(d) E ₊₂₅	(d) F _{-0,76}	Part No.: Bulk package	Part No.: (e) Single package
9	31,19	16,79	25,00 ^{+0,12} _{-0,10}	6,12	8,23	12,93	165X14719X	165X14719XE
15	39,52	25,12	33,30 ^{+0,15}	6,12	8,23	12,93	165X14729X	165X14729XE
25	53,42	38,84	47,04 ^{±0,13}	5,99	8,23	12,93	165X14739X	165X14739XE
37	69,70	55,30	63,50 ^{+0,13} _{-0,11}	5,99	8,23	12,93	165X14749X	165X14749XE
50	67,31	52,68	61,10 ^{+0,14} _{-0,11}	5,99	10,95	15,75	165X14759X	165X14759XE

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm
1 x e	Ä4033	30.06.2011	K.H.	appd.	10.09.01	
3 x d	Ä3662	23.08.2010	K.H.	norm	DIN 41652	
1 x c	Ä1912	06.04.2004	Lehmen	d-old		
3 x b	Ä1788	06.06.2004	Lehmen			
a	Origin					
rev.	description	date	name			

CONEC®

scale:	2:1	
material:	SEE NOTES	
title:	HOOD 9 - 50pos. FOR SOCKET CONNECTOR water resiatant, shielded for EMI/RFI	
dwg no:	Inventor 10	DIN-A4
	16K1A291A	sh: 1
part no:	SEE TABLE	