

Current refinements (click to remove)

Search Tips

Region **USA** Product Family **HSTT Heat Shrink on 25 ft. Reels** Text Search: 'HSTT25-QC'

Your search criteria matched only one product, shown below.



Flexible Polyolefin DRYSHRINK™ Heat Shrink Tubing in 25 ft. Reels

- General purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range:-67°F to 275°F (-55°C to 135°C)
- Flammability Rating: Flame Retardant EXCEPT Clear
- Voltage: 600V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

Part Number:	HSTT25QC
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink
Material:	Polyolefin cross-linked
Color:	Clear
Military Specification:	AMS-DTL-23053/5 Class 2
Length Per Reel (ft.):	25
Length Per Reel (m):	7.6
Max. Recovered I.D. (In.):	.125
Max. Recovered I.D. (mm):	3.2
Min. Expanded I.D. (In.):	.250
Min. Expanded I.D. (mm):	6.4
Nominal Diameter / Size:	1/4
Nominal Recovered Wall Thickness (In.):	.025
Nominal Recovered Wall Thickness (mm):	.6
Shrink Ratio:	2:1
Temperature Range:	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.