



HEAT SHRINK PRODUCTS

HEAT SHRINK THIN WALL TUBING

Part Number	Material	Product Type	Shrink Ratio	Operating Temp. & Voltage Rating	Min. Shrink Temp.	Full Recovery Temp.	Flame Retardant	Agency Certification	Military Standard	General Description
QBG	Polyolefin	Thin Wall	2:1	-55°C to +105°C, 600V	90°C	110°C	-	-	-	Flexible, Thin Wall Tubing for Flexible Gas Pipes mm Sizes: 23 to 76.2mm
Q1	Polyolefin	Thin Wall	2:1	-55°C to +105°C, 600V	80°C	100°C	-	-	-	Non Flame-Retardant, General Purpose, Flexible, Glossy Black or Clear mm Sizes: 1.0 to 50mm, Inch Sizes: 3/64" to 2"
Q2-CB	Polyolefin	Ultra Thin Wall	2:1	-55°C to +125°C, 300V	70°C	100°C	VW-1	 242540	-	No PBB's, PBBE's, PBBO's, Low Cadmium and Lead mm Sizes: 1.0 to 10mm, Inch Sizes: 3/64" to 1/2 "
Q2-F	Polyolefin	Thin Wall	2:1	-55°C to +135°C, 600V	70°C	100°C	VW-1	 E236137  242540	SAE-AMS-DTL 23053/5 Class 1 & 3	No PBB's, PBBE's, PBBO's, Very Flexible, Highly Flame-Retardant mm Sizes: 1.2 to 151mm, Inch Sizes: 3/64" to 6 "
Q2-F3X	Polyolefin	Thin Wall	3:1	-55°C to +135°C, 600V	70°C	100°C	VW-1	 E236137  242540	SAE-AMS-DTL 23053/5 Class 1 & 3	No PBB's, PBBE's, PBBO's, Very Flexible, High Shrink Ratio, Highly Flame-Retardant mm Sizes: 1.5 to 39mm, Inch Sizes: 1/16" to 1 1/2"
Q2-F4X	Polyolefin	Thin Wall	4:1	-55°C to +135°C, 600V	70°C	100°C	VW-1	 E236137  242540	SAE-AMS-DTL 23053/5 Class 1 & 3	No PBB's, PBBE's, PBBO's, Very Flexible, High Shrink Ratio, Highly Flame-Retardant mm Sizes: 19.1 to 115mm, Inch Sizes: 3/4" to 4 1/2"
Q2-F2X(YG) Q2-F3X(YG)	Polyolefin	Thin Wall	2:1, 3:1	-55°C to +135°C, 600V	70°C	100°C	VW-1	 E236137  242540	SAE-AMS-DTL 23053/5 Class 1 & 3	Yellow-Green Striped, Flexible, Flame-Retardant Tubing 2:1 - mm Sizes: 1.2 to 101.6mm, Inch Sizes: 3/64" to 4", 3:1 - 1.6 to 39mm, Inch Sizes: 1/16" to 1 1/2"
Q2-HF	Polyolefin	Thin Wall	2:1	-55°C to +105°C, 600V	70°C	100°C	-	 242540	SAE-AMS-DTL 23053/5	Halogen Free Polyolefin Tubing, Low Smoke mm Sizes: 1.0 to 150mm
Q2-LS	Polyolefin	Thin Wall	2:1	-45°C to +125°C, 600V	65°C	95°C	MVSS 302	 242540	-	Very Flexible, Low Shrink Temperature, Halogen Free Polyolefin Tubing mm Sizes: 1.6 to 50.8mm, Inch Sizes: 1/16" to 2 "
Q2-R	Polyolefin	Semi-Rigid Thin Wall	2:1	-45°C to +135°C, 600V	90°C	130°C	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/5 Class 1 & 3	Semi-Rigid Flame-Retardant Tubing, Resistant to Common Chemicals and Solvents mm Sizes: 1.2 to 25.4mm, Inch Sizes: 3/64" to 1"
Q2-Z	Polyolefin	Thin Wall	2:1	-55°C to +125°C, 600V	70°C	100°C	VW-1	 E236137  242540	-	Environment Friendly, Flexible, Flame-Retardant mm Sizes: 1.0 to 150mm, Inch Sizes: 3/64" to 6 "
Q2-3X	Polyolefin	Thin Wall	3:1	-55°C to +125°C, 600V	70°C	100°C	VW-1	 E236137  242540	-	Flexible, High Shrink Ratio, Highly Flame-Retardant mm Sizes: 1.5 to 39mm, Inch Sizes: 1/16" to 1 1/2"
Q2-XT Q2-XT(HF)	Polyolefin	Thin Wall	Non-Shrink	-55°C to +125°C, 600V	80°C	80°C	VW-1	-	-	No PBB's, PBBE's, PBBO's, Non-Shrink, Irradiated Flexible, Flame-Retardant, (HF) Version is Halogen Free Size: AWG 18 to 1/2"
Q-150K	Modified PVDF	Flexible Thin Wall	2:1	-55°C to +150°C, 600V	135°C	150°C	VW-1	 E245010	SAE-AMS-DTL 23053/18	Black, Flexible, High Temperature, Chemical Resistant, Polyvinylidene Fluoride(PVDF) Kynar® mm Sizes: 1.2 to 38.1mm, Inch Sizes: 3/64" to 1 1/2 "
Q-175K	PVDF	Semi-Rigid Thin Wall	2:1	-55°C to +175°C, 600V	175°C	-	VW-1	 E245010	SAE-AMS-DTL 23053/8	Clear, High Temperature, Chemical Resistant, Polyvinylidene Fluoride(PVDF) Kynar® mm Sizes: 1.2 to 25.4mm, Inch Sizes: 3/64" to 1"
Q-200E Q-200E(TW)	Modified Fluorelastomer Viton®	Very Flexible Thin Wall	2:1	-55°C to +200°C, 600V	150°C	175°C	VW-1	 E245010	SAE-AMS-DTL 23053/13	Flexible, Elastic, High Temperature, Solvent Resistant, Viton® Q-200E - mm Sizes: 3.2 to 50.8mm, Inch Sizes: 1/8" to 2", Q-200E(TW) - mm Sizes: 9.5 to 50.8, Inch Sizes: 3/8" to 2"
Q-PTFE	Modified PTFE	Semi-rigid Thin Wall	2:1	-65°C to +260°C, 600V	-	350°C	Self-extinguish	-	SAE-AMS-DTL 23053/12	Polytetrafluoroethylene Tubing Sizes: AWG 20 to AWG 0
QDR QDR(TW)	Modified Elastomer	Very Flexible Thin Wall	2:1	-75°C to +150°C, 600V	-	175°C	VW-1	-	SAE-AMS-DTL 23053/16	Diesel Resistant Elastomer QDR - mm Sizes: 3.2 to 76.2, Inch Sizes: 1/8" to 3"; QDR(TW) - mm Sizes: 2.4 to 38.1, Inch Sizes: 3/32" to 1 1/2"

HEAT SHRINK MEDIUM / HEAVY WALL TUBING - ADHESIVE LINED

Q5-2X	Polyolefin	Dual Wall	2:1	-45°C to +125°C, 600V	100°C	125°C	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/4	Adhesive-Lined, Flexible, High Shrink Ratio, Flame-Retardant Tubing mm Sizes: 3.2 to 38.1mm, Inch Sizes: 1/8" to 1 1/2"
Q5-3X	Polyolefin	Dual Wall	3:1	-45°C to +125°C, 600V	80°C	120°C	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/4	Adhesive-Lined, Flexible, High Shrink Ratio, Flame-Retardant Tubing mm Sizes: 3.0 to 50.0mm, Inch Sizes: 1/8" to 2 "
Q5-4X	Polyolefin	Dual Wall	4:1	-45°C to +125°C, 600V	80°C	125°C	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/4	Adhesive-Lined, Flexible, High Shrink Ratio, Flame-Retardant Tubing mm Sizes: 4.0 to 52.0mm, Inch Sizes: 3/16" to 2 "
Q5-F3X	Polyolefin	Dual Wall	3:1	-55°C to +125°C, 600V	100°C	-	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/4	Adhesive-Lined, Flexible, Polyolefin Tubing mm Sizes: 3.0 to 40mm, Inch Sizes: 1/8" to 1 1/2"
Q5-F4X	Polyolefin	Dual Wall	4:1	-55°C to +125°C, 600V	100°C	-	Self-extinguish in 30 seconds	 E236137  242540	SAE-AMS-DTL 23053/4	High Shrink Ratio, Adhesive-Lined, Flexible, Flame-Retardant Tubing mm Sizes: 4 to 52mm, Inch Sizes: 3/16" to 2 "

Q5-2X

RoHS
Compliant**DUAL WALL, ADHESIVE LINED, FLEXIBLE POLYOLEFIN TUBING**
SHRINK RATIO 2:1

Features/Applications

Heat shrinkable dual wall adhesive lined tubing is manufactured by co-extrusion of polyolefin and hot-melt adhesive. Designed to provide both insulation and sealing for protection against water and moisture of auto wires, shipping cables, metal tubes and bundled wires.

- Operating temperature: -45°C to +125°C
- Minimum shrink temperature: 100°C
- Full recovery temperature: 125°C
- Approval:  File No. E236137,  242540
- Meets: Sony-SS-00259, SAE-AMS-DTL-23053/4
- Standard color: Black
- Special colors: Red, blue, white, yellow, clear(non-flame retardant jacket)
- RoHS Compliant



Technical Data

Property	Test Method	Typical Data
Tensile Strength	ASTM D 2671	10.4 MPa (min.)
Tensile Strength After Aging	ASTM D 2671	158°C, 168 hrs., remains 70%
Elongation at Break	ASTM D 2671	200% (min.)
Elongation at Break After Aging (158°C, 168 hrs.)	ASTM D 2671	100% (min.)
Longitudinal Shrinkage	UL 224	0 to -10%
Heat Shock	250°C, 4 hrs.	No cracking, no dropping
Cold Bend (-30°C, 1 hr.)	ASTM D 2671	No cracking
Voltage Withstand (AC 2500V, 60 seconds)	ASTM D 2671	No breakdown
Break Down Voltage	ASTM D 2671	AC 2500V (min.)
Volume Resistance	ASTM D 876	Min. 10 ¹⁴ Ω.cm (min.)
Flammability	SAE-AMS-DTL-23053/4	Self extinguish in 30 seconds
Copper Corrosion (158°C, 168 hrs.)	UL 224	Pass
Water Absorption	ASTM D 570	< 0.5%

Product Dimensions

Size		As Supplied (mm)		After Recovered (mm)			Standard Packaging		
Inch	mm	Inside Diameter (min.)	Inside Diameter (max.)	Total Wall Thickness (nom.)	Adhesive Thickness (nom.)	Standard Spool *(SS) (Meter)	Cut to Length Pcs. *(QB)		Qty per bag
							6"	48"	
1/8	3.2/1.6	3.20	1.6	0.70	0.20	200	28	25	
3/16	4.8/2.4	4.80	2.4	0.70	0.20	100	24	25	
1/4	6.4/3.2	6.40	3.2	0.75	0.20	100	20	25	
3/8	9.5/4.8	9.50	4.8	0.75	0.20	50	16	25	
1/2	12.7/6.4	12.70	6.4	0.75	0.20	25	14	5	
3/4	19.1/9.6	19.10	9.5	0.90	0.20	25	12	5	
1	25.4/12.7	25.40	12.7	1.10	0.20	25	8	5	
1 1/2	38.1/19.0	38.10	19.0	1.10	0.20	25	5	5	