

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390122](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: DeviceNet D-Net Open (Female) with Screws to Mini-Change Cordset, 5 Poles, Male (90°), 22 AWG, PVC Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130039](#)
Connector End A D-Net Open
Connector End B Micro-Change (M12)
IP Rating IP20
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name DeviceNet, Mini-Change
Region Europe
Type Double Ended
UPC 78678859056

Physical

Cable Diameter N/A
Cable Length 1.0m (3.28')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Female-Male
Keyway None
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body TPE
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Orientation 90° to Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 22
Wire/Cable Type E152210

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC

Material Info

Engineering Number DND49A-M010

Reference - Drawing Numbers

Sales Drawing SD-130039-030



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130039](#) Series