


Tab Contacts Symmetric (continued)

Tabs 2.8 x 0.8 mm
with Modified
Steel Top Spring,
Mates with
Junior Power Timer

Product Group Drawing:
1355364

Product Specification:
108-18063

Application Specification:
114-18051



Standard Tab Contacts with Modified Spring

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.2–0.5	–	1.15–1.60	1-xxx-3 / 2-xxx-1	964292	4,000	964291	500	x-878950-x	539664-2
0.5–1.0	–	1.4–2.1	1-xxx-3 / 2-xxx-1	964294	4,000	964293	500	x-878937-x	
1.25–2.50	–	2.2–3.0	1-xxx-3 / 2-xxx-1	964296	3,300	964295	500	x-878704-x	

Tab Contacts with Modified Spring and Single Wire Sealing System – Use Seals from Page 54 above

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.2–0.5	–	1.15–1.60	1-xxx-3 / 2-xxx-1	964298	3,500	964297	500	x-878952-x	539650-2
0.5–1.0	–	1.4–2.1	1-xxx-3 / 2-xxx-1	964300	3,500	964299	500	x-878953-x	
1.25–2.50	–	2.2–3.0	1-xxx-3 / 2-xxx-1	964302	3,500	964301	500	x-878954-x	

*) Material and Finish:
1-xxx-3 = CuSn, selective gold plated
2-xxx-1 = CuFe, pre-tin plated

*) The pre- and suffix for the appli-
cators depends on the applied
termination equipment.