




OGA DIAGONAL: 27.22 [691.39]
VA DIAGONAL: 26.52 [673.61]
PA DIAGONAL: 24.98 [634.49]

TOP LEVEL NUMBER	US NUMBER	CHINA NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9501-205	98-0003-3115-1	59-0000-0204-4	FFC	8.00" [203.20]	AG500	23655
17-9501-226	98-0003-3117-7	59-0000-0205-1	USB R	8.00" [203.20]	AG500	23655
17-9501-227	98-0003-3118-5	59-0000-0206-9	SER	8.00" [203.20]	AG500	23655
17-9501-206	98-0003-3116-9	N/A	NOV	SEE DWG	AG500	23655



ESD CLAMSHELL CASE IS USED WITH ALL NOV, USB AND SER TERMINATIONS.

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 1727±10%
2. NICOMATIC HOUSING P/N: OLO5
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

UNITS INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED
.X ±
.XX ±.03 [.76]
.XXX ±.015 [.38]
ANGLES ±1°



DO NOT SCALE DRAWING

SCALE 1 = 1



3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN MTD 5/13/08

D	REVISE	PER	CO	034264	2/12	SB
C	REVISE	PER	CO	033640	10/11	SB
02	REVISE	PER	CO	030452	6/09	SB
REV	CHANGE NOTICE				DATE	DRW

MARKETING DRAWING SCT32NN 26.52" W					
CAD FORMAT AUTOCAD			SHEET 1 OF 1		
SIZE C	DOCUMENT NO. 35704-MKT				REV D