

長蝶番

CONTINUOUS HINGES

B-20257・B-35821～
ステンレス製・鉄製

特 徴 Feature

- 用途に応じた材質が選べます。
- 切断して使用できます。
- Suitable material can be selected according to the purpose.
- Can be cut optionally.

仕 様 ●材 質: 熱間圧延鋼板(SPHC)
冷間圧延鋼板(SPCC) (軸はステン
レス製)
ステンレス鋼板(SUS304)

●表面仕上: SPCC・SPHC/
亜鉛めっきクロメート処理(MFZn-C)

用 途 ●航空機・通信機器・測定機器・船舶・車両・小型
コンテナなどの筐体

●標準品・・・納期お問合せください

●航空機にはMS規格品をご使用ください。

●必要な寸法に切断後軸にカシメ等の抜け止め加工をしてご使用ください。

●両端に抜け止め加工を行う場合は、必ず同じ羽根で行ってください。異なる羽根で行うと作動不良の原因となります。

●長尺商品のため、送料が掛かります。詳細はお問合せください。

Speci- ●Material: Hot rolled steel plate (SPHC)
fications Cold rolled steel (SPCC)
(The axle is stainless steel)
Stainless steel (SUS304)

●Finish: SPCC, SPHC:

Zinc plating chromate treatment
(MFZn-C)

Specifi- ●Communication devices, measurement
c-use devices, ships, specially equipped
vehicles, construction machinery, small
containers.

Remarks ●The MS (Military Standard) articles
must be used for the air crafts.



●The hinge is not processed to prevent
extraction of the shaft. After cutting
the hinge to size and before use, fix
stops, etc., on the shaft to prevent its
extraction.

●When fixing stops on both ends,
always fix on the same wing. Fixing
on different wings may cause faulty
operation.


B-35825-14D

B-35822-12C


商品番号 Product No.	RoHS	CAD	備考 Remarks	L1	L2	W	t	φD	製品質量(g) Mass	コード Code	単 価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
B-20257-C1	●			1829	15	19	0.8	2.0	315	11134	¥9,600	5個～	¥9,216
B-20257-C2	●			1829	15	27	1.0	3.0	570	11135	¥9,600	5個～	¥9,216
B-20257-C3	●			1829	15	32	1.2	3.0	760	11136	¥9,600	5個～	¥9,216
B-20257-C4	●			1829	15	38	1.5	3.0	1,100	11137	¥13,000	5個～	¥12,480
B-20257-C5	●	3D		1829	15	51	1.5	5.0	1,580	11138	¥13,000	5個～	¥12,480
B-20257-C6	●			1829	50	51	1.5	5.0	1,610	11139	¥13,000	5個～	¥12,480
B-35822-10C	●			1829	15	32	1.0	3.0	630	11147	¥12,000	5個～	¥11,400
B-35822-11C	●			1829	15	38	1.0	3.0	730	11148	¥12,000	5個～	¥11,400
B-35822-12C	●		SUS 304	1829	15	51	1.0	3.0	885	11149	¥12,000	5個～	¥11,400
B-35823-6C	●			1829	15	38	1.2	3.0	850	11152	¥14,000	5個～	¥13,440
B-35823-7C	●			1829	15	51	1.2	3.0	1,060	11153	¥14,000	5個～	¥13,440
B-35825-14C	●			2133	25	38	1.5	3.0	1,245	11157	¥15,000	5個～	¥14,400
B-35825-15C	●			2133	25	51	1.5	3.0	1,560	11158	¥15,000	5個～	¥14,400
B-35825-16C	●			2133	25	64	1.5	3.0	1,880	11159	¥15,000	5個～	¥14,400
B-35829-16C	●			2133	50	51	2.0	6.0	2,600	11169	¥15,000	5個～	¥14,400
B-35829-18C	●			2133	50	76	2.0	6.0	3,490	11170	¥15,000	5個～	¥14,400
B-35829-20C	●			2133	50	102	2.0	6.0	4,230	11171	¥15,000	5個～	¥14,400
B-35831-6C	●	2D		2133	50	102	3.0	10.0	7,500	11178	¥20,000	5個～	¥19,200
B-35821-8D				1829	15	27	0.8	2.0	405	11140	¥4,100	5個～	¥3,936
B-35821-10D				1829	15	38	0.8	2.0	530	11141	¥4,100	5個～	¥3,936
B-35822-9D	●			1829	15	27	1.0	3.0	615	11142	¥4,100	5個～	¥3,936
B-35822-10D	●		SPCC	1829	15	32	1.0	3.0	670	11143	¥4,200	5個～	¥3,990
B-35822-11D	●			1829	15	38	1.0	3.0	755	11144	¥4,300	5個～	¥4,085
B-35822-12D	●			1829	15	51	1.0	3.0	950	11145	¥4,400	5個～	¥4,180
B-35823-6D	●			1829	15	38	1.2	3.0	875	11150	¥6,000	5個～	¥5,760
B-35823-7D				1829	15	51	1.2	3.0	1,115	11151	¥6,000	5個～	¥5,760
B-35825-14D				2133	25	38	1.6	3.0	1,435	11154	¥6,000	5個～	¥5,700
B-35825-15D				2133	25	51	1.6	3.0	1,680	11155	¥6,000	5個～	¥5,700
B-35825-16D				2133	25	64	1.6	3.0	2,035	11156	¥6,000	5個～	¥5,700
B-35826-10D				2133	25	38	1.6	5.0	1,630	11160	¥6,000	5個～	¥5,700
B-35826-11D				2133	25	51	1.6	5.0	1,960	11161	¥6,000	5個～	¥5,700
B-35826-12D				2133	25	64	1.6	5.0	2,345	11162	¥6,000	5個～	¥5,700
B-35829-11D				2133	50	51	2.0	5.0	2,500	11163	¥6,000	5個～	¥5,700
B-35829-13D				2133	50	76	2.0	5.0	3,310	11164	¥6,000	5個～	¥5,700
B-35829-15D			SPHC	2133	50	102	2.0	5.0	4,185	11165	¥6,200	5個～	¥5,890
B-35829-16D				2133	50	51	2.0	6.0	2,690	11166	¥6,200	5個～	¥5,890
B-35829-18D				2133	50	76	2.0	6.0	3,520	11167	¥6,200	5個～	¥5,890
B-35829-20D				2133	50	102	2.0	6.0	4,300	11168	¥6,200	5個～	¥5,890
B-35830-11D				2133	50	76	2.3	6.0	4,030	11172	¥9,000	5個～	¥8,640
B-35830-13D				2133	50	102	2.3	6.0	4,870	11173	¥9,000	5個～	¥8,640
B-35830-14D				2133	50	127	2.3	6.0	5,870	11174	¥10,000	5個～	¥9,500
B-35831-6D				2133	50	102	3.2	10.0	7,980	11175	¥10,000	5個～	¥9,500
B-35831-7D				2133	50	127	3.2	10.0	9,205	11176	¥11,000	5個～	¥10,450
B-35831-8D				2133	50	153	3.2	10.0	10,800	11177	¥12,000	5個～	¥11,400

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。



軸はステンレス製です。Shaft is made of stainless steel

使用例
Example of
application

CONTINUOUS HINGES

長蝶番

平蝶番

裏蝶番

抜き差し
蝶番段付
蝶番クリーン
ヒンジ特装車
蝶番フリーザー
ヒンジ特殊
蝶番トルク
ヒンジ

ステー

周辺機器
(B)