






DIMENSIONS: mm (In.)**Solder Terminals****Operating Characteristics****Contact Configuration****Mounting Holes****Electrical Specifications:**

- Electrical Operation Frequency: 10~30 operations/min
- Electrical Life: 6,000~50,000 operations
- Rating: 6A/125-250VAC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100mΩ min. at 500VDC
- Dielectric Strength: 1,000VAC RMS (50-60HZ)

Mechanical Specifications:

- Mechanical Operating Frequency: 120 operations/min
- Mechanical Life: 2,000,000 operation Min.

Operating Characteristics:

- OF Max. (g): 203
- Op (mm): 8.4 ±0.3
- PT Max. (mm): 1.2
- OT Min. (mm): 0.6
- MD Max. (mm): 0.2
- FP Max. (mm): 9.3
- RF Max. (g): 50

Sealed Snap Switch
SNS72-06-203XX -S01

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-72-06-203XX-S01](#)