

You are here: Applied Computing & Systems > Display Solutions > ES-1000 LCD Kits > **ES-1110N-LSAE**

ES-1110N-LSAE

RoHS

[Email page](#)

[Live Chat](#)

10.4" Color TFT-LCD Kit for LVDS Interface



Main Features

- LCD Panel: AUO G104SN03
- Display: 800 x 600 SVGA, 262K
- Viewing Angle (L/R/U/D): 60/60/35/65
- Brightness (nit): 230
- Response Time (ms): 35
- Backlight (hrs.): CCFL, 2-tubes, 20,000 hrs
- Operation Temp.: 0 ~ 50 °C
- ES-1110N-LSA-01E ~ 04E LCD Kit Cable Length (mm): 500 (optional)
- Outline Dimensions mm (W x H x D): 236 x 174.3 x 5.6

Datasheet (PDF)

Manual/ Driver/ BIOS/ FAQ

Introduction

10.4" Color TFT-LCD Kit for LVDS Interface

Ordering Information		
Part Number	Description	
ES-1110N-LSA-01E	RoHS	10.4" LCD kit, AUO 230 nites, LVDS-1, SVGA
ES-1110N-LSA-02E	RoHS	10.4" LCD kit, AUO 230 nites, LVDS-2, SVGA
ES-1110N-LSA-03E	RoHS	10.4" LCD kit, AUO 230 nites, LVDS-3, SVGA
ES-1110N-LSA-04E	RoHS	10.4" LCD kit, AUO 230 nites, LVDS-4, SVGA
ES-1110N-LSAE	RoHS	10.4" LCD kit, AUO 230 nites, LVDS, SVGA

Contact Information		
Office	Phone	Email

Rate this page :

Did the information help you achieve your goal?

☐ Yes

☐ No

* Your eMail address:

Your Company

* Your Country:

Afghanistan

Please provide us with comments to help improve this page:

Submit

eCatalog

Whitepaper

- Stimulus Spending Brings Medical Applications to Life: Opportunities and Challenges in Digital Records
- Industrial-Grade Advantech Digital Signage Solutions for Mission-Critical Digital Signage Deployments
- On the Road with Fleet Management
- Advantech Digital Video Solutions: Industrial Strength For 24/7 Operation
- Advantech Medical Computing Enabling Digital Healthcare
- What would you do with a TDP of less than 5 watts?

Services

- [Buy Online](#)

- Featured Articles
- Panel PC, Flat Panel Computer, Touch Screen, Human Machine Interface
 - Industrial Computer
 - Fanless PC, Compact PC, Rugged PC, Embedded System, Panel PC