


Material: Nylon66 UL94V-0

Odering Information:



5700S**M0*0
1 2

1. No. of circuit
2. 0=Black W=White



RoHS COMPLIANT



2P



3~7P



Circuits	Part No.	Dim.A	Dim.B	Dim.C
3	5700S03M0*0	5.00(.197)	8.1(.319)	10.6(.417)
4	5700S04M0*0	7.50(.295)	10.6(.417)	13.1(.516)
5	5700S05M0*0	10.00(.394)	13.1(.516)	15.6(.614)
6	5700S06M0*0	12.50(.492)	15.6(.614)	18.1(.713)
7	5700S07M0*0	15.00(.590)	18.1(.713)	20.6(.811)

E	ES110320			 LEOCO CORPORATION	APPROVED:		PART NO.:			
D	ES101218				DATE:		5700S**M0*0			
C	ES081001				GENERAL TOLERANCES: (UNLESS SPECIFIED)		CHECKED:		TITLE: HOUSING	
B	ES030329									
A	DWG REL				DRAWN:		DRAWING NO.:			
REV.	ECO. NO.	CHG.	APP.					570001S		