

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14

P4

REVISED PER ECO-11-004917

11MAR11

RK

HMR

10.69 MAX
[.421]
WASHER R

DIMPLED SURFACE

BODY

SLEEVE

37.64 MAX
[1.482]

43.66 MAX
[1.719]

11.89
[.468]

Ø5.00±0.08
[.197±.003]
(FOR #10 STUD)

1

2

3

4

5

6

7

AMP
WIRE RANGE

6 AWG
STRANDED

FILE
E13288

6 AWG
STRANDED

LR7189
Certified

6 AWG
STRANDED

1

2

3

4

5

6

7

STAMP AMP 6* LOCATE APPROX AS SHOWN

TONGUE MATERIAL THK 1.14±0.08[.045±.003]

SEE TABLE FOR WIRE INSULATION DIA MAX

FOREIGN PRODUCTION ONLY

TAPE ITEMS ARE ON 30.48[1.200] CENTERS

SUPERSEDED BY 8-52265-5

OBSOLETE PARTS

11.07
[.436]

20

LOOSE PC,BOX SPL

8-52265-6

9.14
[.360]

500

ON TAPE

52265-4

11.07
[.436]

500

ON TAPE

52265-3

9.14
[.360]

-

LOOSE PC

52265-1

11.07
[.436]

100

LOOSE PC

52265

WIRE
INSULATION
DIA

QTY

PACKAGE TYPE

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
105° C

THIS DRAWING IS A CONTROLLED DOCUMENT.

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

VOLTAGE RATING:
600 V MAX

CIRCULAR MIL AREA:
10.54-16.77mm² [20,800-33,100]
STRANDED

MATERIAL
COPPER PER ASTM B-152
PVC, COLOR: BLUE

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

TIN PLATE PER ASTM-B545

DWN
S.S. GOULDEN
9-29-93

CHK
R. HERSEY
9-29-93

APVD
M ELLIS
9-29-93

PRODUCT SPEC
NOT AVAILABLE

APPLICATION SPEC
114-2161

WEIGHT
-

TE Connectivity

NAME
TERMINAL, RING TONGUE,
PLASTI-GRIP
WIRE SIZE: 6 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-52265

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
P4

1470-19 (3/11)