UNSHIELDED PLASTIC or TPE JACKETED MINIATURE CORDS UL LISTED

Stranded tinned copper, polypropylene insulated, black PVC jacketed.
Temperature Rating: -20C + 80C

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
6516P	48,36,24,12	2	28	300	7/36	1/2	.140	1/2
6517P	48,36,24,12	3	28	120	7/36	1/2	.150	1/2
6518P	48,36,24,12	4	28	120	7/36	1/2	.155	1/2
6519P	48,36,24,12	5	28	120	7/36	1/2	.165	9/16
6520P	48,36,24,12	6	28	120	7/36	1/2	.180	5/8
6521P	48,36,24,12	7	28	120	7/36	1/2	.180	5/8
6522P	48,36,24,12	8	28	120	7/36	1/2	.195	5/8

RETRACTED - EXTENDED RATIO (1 TO 5)

48" - 20'	**36" - 15'**	**24" - 10'**	**12" - 5'**

STRAIGHT LEAD LENGTHS

6"	**6"**	**6"**	**12"**

UNSHIELDED PLASTIC or TPR JACKETED COMMUNICATIONS & ELECTRONIC CONTROL CORDS



UL LISTED

Stranded tinned copper, polypropylene insulated, PVC or TPR jacketed.
Temperature Rating: -20C + 80C

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	NOM. AREA (mm)	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
* **6370P** ** **6382P**	48,36,24,12	2	23	300	.259	21/36	1	.180	5/8
* **6371P** ** **6383P**	48,36,24,12	3	23	120	.259	21/36	1	.190	11/16
* **6372P** ** **6384P**	48,36,24,12	4	23	120	.259	21/36	1	.200	11/16
* **6373P** ** **6385P**	48,36,24,12	5	23	120	.259	21/36	1	.215	3/4
* **6374P** ** **6386P**	48,36,24,12	6	23	120	.259	21/36	1	.230	7/8
* **6375P** ** **6387P**	48,36,24,12	7	23	120	.259	21/36	1	.230	7/8
* **6376P** ** **6388P**	48,36,24,12	8	23	120	.259	21/36	1	.245	7/8
* **6377P** ** **6389P**	48,36,24,12	10	23	120	.259	21/36	1	.280	15/16
* **6378P** ** **6390P**	48,36,24,12	12	23	120	.259	21/36	1	.285	1
* **6379P** ** **6391P**	48,36,24,12	15	23	120	.259	21/36	1	.310	11/16

*Black PVC jacket
**Black TPR jacket