


SEAM-20-01-L-06-2-RA-GP-TR



SEAM-30-02.0-L-04-2-A-GP-K-TR

(1.27 mm) .050"

SEAM-RA, SEAM-GP SERIES

HI-DENSITY RIGHT-ANGLE OPEN-PIN-FIELD

SEAM-RA Mates with:
SEAF, SEAF-RA, SEAFP
SEAM-GP Mates with:
SEAF-RA-GP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SEAM-RA or www.samtec.com?SEAM

Insulator Material:
Black LCP

Contact Material:
Copper Alloy

Current Rating:
SEAM-RA = 1.9 A per pin
(10 pins powered)
Operating Temp Range:
-55 °C to +125 °C

Plating:
Au or Sn over
50 μ" (1.27 μm) Ni

Working Voltage:
SEAM-RA = 260 VAC
SEAM-GP = 240 VAC

Mated Cycles:
SEAM-GP = 100

RoHS Compliant:

Yes
Lead-Free Solderable:
Yes



RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Notes:
SEAM-GP Patented

Some sizes, styles and options are non-standard, non-returnable.



ALSO AVAILABLE (MOQ Required)

- Extended Guide Post
- Guide post field termination kits
- Other platings

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.