


Wiha ESD Safe Protturn Pliers & Cutters

Surface resistance of handles is $10^6 - 10^9$ Ohms

ESD Safe Bent Nose Pliers



45813 Protturn ESD Safe Bent Nose Pliers


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45813	mm	Inch	A	B	C	Pkg.	lbs.
	152	6.0	2mm	30mm	4mm	1	.18

[SHOP](#)

ESD Safe Round Nose Pliers



45814 Protturn ESD Safe Round Nose Pliers


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45814	mm	Inch	A	B	C	Pkg.	lbs.
	152	6.0	2mm	22mm	3mm	1	.17

[SHOP](#)

ESD Safe Diagonal Cutters



45820 Protturn ESD Safe 21° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45820	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	127	5.0	18/1mm	13mm	12mm	3mm	1	.16

[SHOP](#)

ESD Safe Diagonal Cutters



45821 Protturn ESD Safe 45° Precision Cutters/Flush Cut


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45821	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	127	5.0	18/1mm	10mm	9mm	2mm	1	.14

[SHOP](#)

ESD Safe Diagonal Cutters



45822 Protturn ESD Safe 21° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45822	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	140	5.5	16/1.3mm	13mm	12mm	3mm	1	.15

[SHOP](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiha:

[45814](#) [45813](#) [45822](#) [45820](#) [45821](#)