

## HEYCO

### Heyco® RDD Lockit™ Strain Relief Bushings – Right Angle


Snap onto **Round Cables** for Faster Assembly into **Double D** Mounting Holes - *Semi-Automatic Equipment Available*

- **Right Angle design eases the cable into the bend**, prevents kinking and assures longest cable and product life.
- Assembly friendly! Independent of insertion into the panel, RDD Lockit™ Strain Reliefs self-lock onto the cable. Preassemble RDD Lockits off line for final assembly at a later time or remote location, for lower installed cost!
- Install easily with fingertip pressure into a standard round or Double D hole. No tools required, even for hand assembly.
- Protect the lifeline of your electric/electronic products by absorbing the forces of push and pull that may be exerted on the flexible power cord. Double D design eliminates the possibility of part rotation under forces of twist.
- Multiple panel locking steps secure Lockit Strain Reliefs into a wide range of panel thicknesses for a **flush, finished fit**.
- Heyco's automated Pre-Assembly Equipment speeds assembly of the RDD onto the cable and thus lowers costs while greatly reducing risk of carpal tunnel syndrome. See pages 4-15 & 4-16.
- Consult Heyco for other wire types and sizes.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.

WILL FIT THESE CABLES				PANEL DIMENSIONS				RDD LOCKIT STRAIN RELIEF for Faster Assembly		Corresponding Mounting Hole Plug	
UL Type	AWG/Conductors	Approximate Size		Mounting Hole Size		Thickness		PART NO. Black	PART NO. White	PART NO.	DESC.
AWM, SJTO & SJ	18/3	.130-.210	3.3-5.3	.625 w/.550 flats	15.9 w/14.0 flats	.032 .040 .048 .063 .099	0.8 1.1 1.2 1.6 2.5	1816	1817	RDD 101A-90	2497 DD 625-550
See table on page 4-10	various	.220-.290	5.6-7.4	.625 w/.550 flats	15.9 w/14.0 flats	.032 .040 .048 .063 .099	0.8 1.1 1.2 1.6 2.5	1818	1819	RDD 101-90	2497 DD 625-550
See table on page 4-10	various	.290-.385	7.4-9.8	.875 w/.770 flats	22.2 w/19.6 flats	.032 .063 .099 .126 .157	0.8 1.6 2.5 3.2 4.0	1820	1821	RDD 201-90	2509 DD 875-770
See table on page 4-10	various	.340-.430	8.6-10.9	.875 w/.770 flats	22.2 w/19.6 flats	.032 .063 .099 .126 .157	0.8 1.6 2.5 3.2 4.0	1824	1825	RDD 301-90	2509 DD 875-770

Standard color black. Consult Heyco for white and other colors.

Locking Tab varies with Cable Size



Quick  
Specs

Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories File E15331
	Certified by the Canadian Standards Association File 8919
Flammability Rating	94V-2
Temperature Range	-04°F (-18°C) to 221°F (105°C).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1816](#) [1817](#) [1818](#) [1819](#) [1820](#) [1821](#) [1824](#) [1825](#)