

FEATURES AND OPTIONS

- Accepts JEDEC leaded type PLCCs
- Available in positions 20, 28, 32, 44, 52, 68, and 84
- Available in either tin or gold plating

SPECIFICATIONS

MATERIALS

Contact: Phosphor Bronze

Insulator: PBT with 30% glass fiber (UL94V-0)

ELECTRICAL


Current rating: 1 A minimum

Voltage: AC500V r.m.s.

Insulation resistance: 1000M ohm minimum

Contact resistance: 30 milliohms maximum

Operating temperature range: -55°C to +105°C



DIMENSIONS

# of pins	A	B	C	D
20	5.08 .200	15.58 .614	18.30 .720	10.16 .400
28	7.62 .300	18.10 .713	22.20 .874	12.70 .500
32	7.62 .300	18.80 .740	25.70 1.012	12.70 .500
44	10.16 .400	21.30 .839	25.70 1.012	15.24 .600
52	12.70 .500	23.50 .925	29.80 1.173	17.78 .700
52	15.24 .600	26.00 1.024	32.64 1.285	20.32 .800
68	20.32 .800	30.20 1.189	40.10 1.579	25.40 1.000
84	25.40 1.000	35.20 1.386	46.90 1.846	30.48 1.200

HOW TO ORDER

A-CCSXX-X

- Z - Tin plated contacts
- G - Gold plated contacts
- XX - Number of contacts