

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON AND INCANDESCENT TECHNOLOGY

MOUNTING HOLE, Ø 0.310"

| PART NO.                       | LENS COLOR | VOLTAGE    | CURRENT [mA] | RATED LIFE HOURS |
|--------------------------------|------------|------------|--------------|------------------|
| <b>NEON 115VAC SERIES</b>      |            |            |              |                  |
| WL-2110A1                      | RED        | 105-125VAC | 1.5mA        | 25,000           |
| WL-2110A2                      | CLEAR      | 105-125VAC | 1.5mA        | 25,000           |
| WL-2110A3                      | AMBER      | 105-125VAC | 1.5mA        | 25,000           |
| WL-2110A4                      | WHITE      | 105-125VAC | 1.5mA        | 25,000           |
| WL-2112A5                      | GREEN      | 105-125VAC | 1.5mA        | 25,000           |
| WL-2112A6                      | BLUE       | 105-125VAC | 1.5mA        | 25,000           |
| <b>NEON 230VAC SERIES</b>      |            |            |              |                  |
| WL-2111A1                      | RED        | 208-250VAC | 1.5mA        | 25,000           |
| WL-2111A2                      | CLEAR      | 208-250VAC | 1.5mA        | 25,000           |
| WL-2111A3                      | AMBER      | 208-250VAC | 1.5mA        | 25,000           |
| WL-2111A4                      | WHITE      | 208-250VAC | 1.5mA        | 25,000           |
| WL-2113A5                      | GREEN      | 208-250VAC | 1.5mA        | 25,000           |
| WL-2113A6                      | BLUE       | 208-250VAC | 1.5mA        | 25,000           |
| <b>INCANDESCENT 12V SERIES</b> |            |            |              |                  |
| WL-2195A1-12V                  | RED        | 12V-14V    | 80mA         | 25,000           |
| WL-2195A3-12V                  | AMBER      | 12V-14V    | 80mA         | 25,000           |
| WL-2195A4-12V                  | WHITE      | 12V-14V    | 80mA         | 25,000           |
| WL-2195A5-12V                  | GREEN      | 12V-14V    | 80mA         | 25,000           |
| <b>INCANDESCENT 28V SERIES</b> |            |            |              |                  |
| WL-2195A1-28V                  | RED        | 24V-28V    | 40mA         | 25,000           |
| WL-2195A3-28V                  | AMBER      | 24V-28V    | 40mA         | 25,000           |
| WL-2195A4-28V                  | WHITE      | 24V-28V    | 40mA         | 25,000           |
| WL-2195A5-28V                  | GREEN      | 24V-28V    | 40mA         | 25,000           |

## NOTES

1. Minimum panel thickness 0.030"
2. 6" leads with 1/2" strip are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +80°C
4. Ambient temperature  
 $T_A$ : -20°C - +60°C
5. Voltage tolerance  
 $V_{OP}$ : ±10%
6. AC operation only for neon type
7. AC/DC operation for incandescent type
8. Body material  
Nylon, white
9. Lens material  
Polycarbonate
10. Bezel material  
Nylon, white
11. Wire gauge  
18 AWG
12. Wire strip  
1/2"


## CERTIFICATIONS

UL (E340667), RoHS



**RoHS**  
COMPLIANT

## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches

## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

