



NUMBER OF POSITIONS	DIMENSION	
	A	B
06	5.08	12.32
08	7.62	14.86
10	10.16	17.40
12	12.7	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
24	27.94	35.18
26	30.48	37.72
28	33.02	40.26
30	35.56	42.80
34	40.64	47.88
40	48.26	55.5
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

MATERILA&FINISH

insulator:PBT Glass Fiber(UL94V-0)

Contact:Brass

Contact: Tin-Plated Over Nickel

SPECIFICATIONS

Current Rating:1A AV,DC


Voltage Rating:250V AC,DC

Temperature Range:-40°C TO +150°C

Contact Resistance:20mΩ Min

Insulation Resistance:1000mΩ Min

withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.20 ANGLES : ±2° X.X ±0.15 X.XX ±0.10 DO NOT SCALE DRAWING		CnC Tech, LLC Industrial Cable and Connector Technology			
DRAWN BY	Kevin	PART NO.		3030-03-XX-0104	
CHECKED BY		SIZE A	UNIT MM	TITLE 2.54/IDC	REV A0
APPROVED BY		SCALE		THIRD ANGLE PROJECTION 	PAGE 1 OF 1
DWG NO.		ITEM NO.			DATE 2005/07/17