




Scatola di connessione IP68 "Paguro®"

Junction box IP68 "Paguro®"



Per cavi tondi di tipo H05RN-F, H07RN-F, FG7OR, FROR

Codice 5625/08 - Ø min 6.5 - Ø max 8

Codice 5625/10 - Ø min 7.5 - Ø max 10

Codice 5625/12 - Ø min 9.5 - Ø max 12

SPECIFICHE TECNICHE

- Connessione 3x4 mm²
- Tensione nominale: 400V

For round cables type H05RN-F, H07RN-F, FG7OR, FROR

Code 5625/08 - Ø min 6,5 - Ø max 8

Code 5625/10 - Ø min 7,5 - Ø max 10

Code 5625/12 - Ø min 9,5 - Ø max 12



TECHNICAL DETAILS

- Connection 3x4 mm²
- Rated voltage 400V

- ★ Fornito di vite autofilettante 005625/41682: Ø 4,2x16 mm e morsettera 3x4 mm² di 005625/3/427
- ★ Supplied with self threading screws 005625/41682: Ø 4,2x16 mm Terminal block 3x4 mm² 005625/3/427

Componenti connessione



Connection components



Materiale / Material

6 Nylon 66 RV

Codice / Code	Dimensioni / Dimensions (mm)				Colore / Colour		
	A	B	C	D	6 Blu Bleu	7 Verde Green	9 Giallo Yellow
5625/08	95	45	24	8	Materiale / Material →		6
5625/10	95	45	24	10		6	
5625/12	95	45	24	12		6	



Materiale / Material

6 Nylon 66 RV

Codice / Code	Dimensioni / Dimensions (mm)				Colore / Colour	
	A	B	C	E	0 Neutro Natural	6
005625/3/427	31,5	23	20,7	12	Materiale / Material →	6

Esempio di montaggio "Paguro®" Assembly's example "Paguro®"

