




CK14M

Right angle heavy-duty contact surface probe



Copyright © 2007 Test Products International, Inc.

Application

Contact temperatures on flat and uneven high temperature surfaces

Range°F°C

-58° to 1202°F
-50° to 650°C

Probe tip

36

Dimensions

Stem Length: 6" (152mm)
w/90° bend
Diameter: 0.6" (14mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane