



Metal Clad Cable Termination Fittings & Accessories

T&B Catalog Number:

UPC Number:
Status:
Description:

STE200
78621093040
Active

Star Teck Extreme aluminum jacketed cable fittings, hub size-2 in.

Features

- Powergrip grounding ring.
- Removable armor-stop for greater cable ranges.
- Elastomeric collar ring/bushing for greater cable ranges.
- Built-in jacket stripping gauge on gland nut.
- Gland nut can be tightened with hammer and screwdriver.

Application

- Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).
- Form a mechanical grip and water and/or oil-resistant termination.
- Provide grounding continuity of cable armor.

General

Material Aluminum
Strip Length (inches) 1 3/4

Dimension Information

Hub Size (inches) 2
Dimension B (inches) 4.120
Dimension C (inches) 3.600
A1: Throat Diameter Minimum (w/Armor Stop) 1.645
A2: Throat Diameter Minimum (wo/Armor Stop) 1.995
Range Over Jacket -Minimum (inches) 1.825
Range Over Jacket -Maximum (inches) 2.375
Range Over Armor -Minimum (inches) 1.665
Range Over Armor -Maximum (inches) 2.215
Strip Length (inches) 1 3/4

Packaging

Package in Units 5
T&B Sold in UOM Each
T&B Weight Per UOM 154.75 lbs. per 100

Application Support

T&B Instruction Sheets ta01766-tb2
Product Specifications & Overview Available on Website
Product Brochure-Star Teck Extreme Available on Website
Director™ Cable Fittings

Notes

*Note UL Listed watertight NEMA Type 6P

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 38947

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com