

FO connectors - FOC-V14-C1ZNI-B/SJFG:10 - 1408056

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Push-pull connector (version 14), die-cast zinc, with SC-RJ insert for GOF, for cable diameter of 5.5 mm ... 10 mm, cable outlet at the bottom, 10 pcs.

Product Features

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent removal
- Highest ESD and EMC resistance for reliable transmission



Key Commercial Data

Packing unit	1 pc
Custom tariff number	85367000
Country of origin	Germany

Technical data

Mechanical characteristics

Standards/specifications	IEC PAS 61076-3-117
Insertion/withdrawal cycles	≥ 50
External cable diameter	5.5 mm ... 10 mm
Cable exit	angled

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 40 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP67

Material data

Housing material	Zinc die-cast
------------------	---------------

FO connectors - FOC-V14-C1ZNI-B/SJFG:10 - 1408056

Technical data

Standards and Regulations

Standards/regulations	IEC PAS 61076-3-117
-----------------------	---------------------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189239
eCl@ss 6.0	27144001
eCl@ss 7.0	27144001
eCl@ss 8.0	27440101

ETIM

ETIM 3.0	EC000007
ETIM 4.0	EC000489
ETIM 5.0	EC002636

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensional drawing



