

Electronic Professional Pliers

The Best Pliers You'll Ever Use



- High quality ball bearing steel
- 63 - 65 Rockwell Hardness (HRC)
- 2-Component ESD Ergonomic handles, soft comfortable gripping surface, hard plastic core
- Dual leaf springs in blue steel
- Matched bearing rings to minimize metal-metal contact and friction

● Lap joint with screw to achieve a high level of strength and precision

● Static dissipative (10^6 - 10^8 Ω /sq.), oil, grease and wear-resistant

DURATOOL

New

531558

Mfrs. List No.	Jaw	Overall length		Order Code	+	Price Each	
		inch	mm			+	+
Long Snipe Nose							
D01013	Smooth	5.6"	143	169-6527	— —	— —	— —
D01014	Serrated	5.6"	143	169-6528	— —	— —	— —
Snipe Nose							
D01015	Smooth	5.2"	133	169-6529	— —	— —	— —
D01016	Serrated	5.2"	133	169-6530	— —	— —	— —
Flat Nose							
D01017	Smooth	5.2"	133	169-6532	— —	— —	— —
Round Nose							
D01018	Smooth	5.2"	133	169-6533	— —	— —	— —