


Capacitor, film, 0.1 uF, +/-5% Tol, General Purpose, 50VDC@125C



Note: '()' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	5.7	+/-0.2
W	5	+/-0.2
T	4	+/-0.2
F	0.5	NOM

Packaging Specifications	
Package Kind:	T&R
Package Quantity:	2100

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.1 uF
Dielectric:	Metallized PPS
Rated Temperature:	125C
Voltage @ rated temp:	50VDC
Voltage AC:	30VAC
Tolerance:	+/-5%
Body Type:	Surface Mount
Chip Size:	2220 (5750 metric)
Application:	General Purpose
Temperature Range:	-55/+125C
Sub Application:	HighStability
Dissipation Factor @ 1 kHz:	0.15%
Dissipation Factor @ 10 kHz:	0.25%
Dissipation Factor @ 100kHz:	0.5%
Insulation Resistance:	15 GOhm
Maximum dVdT:	6 v/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.