


CABLE TIES AND ACCESSORIES




Part No.	min. Loop Tensile kg	"L" mm	Bundle Ø mm	"W" mm	"T" mm	"A" mm	"B" mm	"C" mm	Hole Ø mm	Panel thickness mm
WIT-30RRA-4	13.5	160.3	31.8	3.6	1.3	7.1	14.3	7.1	4.8	0.8-2.0
WIT-30RRA-8		166.7						13.5		
WIT-30RRA-12		173.0						19.8		
WIT-30RRA-16		179.4						25.4		
WIT-50RLA	22	225.4	50.8	4.8		5.1	5.1	4.8		


WIT30RR/WIT50RLA

SELF MOUNT CABLE TIES

WIT30RRA




WIT50RLA



Note:

WIT	30RRA	4	01
Part	Type	"C"	Material Code


Material: Nylon 6/6 - natural, UL 94 V-2, RMS-01
by special order:
Nylon 6/6-black, UV stabilized,
UL 94 V-2, RMS-46
Std. Pk.: 1.000 pcs.



HT

HANKING TIE

Part No.	Bundle max. mm	"B" mm	"C" mm
HT-3.9	23	81.0	99.0
HT-4.9	28	107.0	125.0
HT-5.9	36	132.0	150.0



Note:

HT	3.9
Part	Length

Material: Polyethylene - natural, RMS-134
Std. Pk.: 1.000 pcs.