




DESCRIPTION: MALE - HIGH DENSITY - MACHINED CONTACTS - SOLDER CUP



ACCEPTS 28 - 24 AWG WIRE



MATERIAL:

SHELL: STEEL MATERIAL, NICKEL FINISH
INSULATOR: PBT THERMOPLASTIC 30% GLASS FILLED, UL 94V-0 RATED, BLACK
CONTACT MATERIAL: BRASS
CONTACT FINISH: SELECTIVE GOLD FINISHED
SEALING MATERIAL: F08 FLEXIBLE ADHESIVE

ELECTRICAL:

CONTACT CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 30 Milliohms Max.
DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
INSULATION RESISTANCE: 5,000 Megohms Min.
TEMPERATURE RATING: -55° ~ +105° C

780-M YY-1 0 3 L YY 1

SERIES _____
MACHINED CONTACTS _____
POSITIONS _____
15 _____
26 _____
44 _____
GENDER _____
1 = MALE _____
TERMINATION _____
0 = SOLDER CUP _____
SHELL PLATING _____
3 = NICKEL _____
RoHS COMPLIANT _____
HARDWARE OPTIONS _____
00 = NO HARDWARE _____
01 = 0.098" 4-40 INSERT, BOARD SIDE _____
PLATING OPTIONS _____
1 = GOLD FLASH, ENTIRE CONTACT _____

DIMENSIONS (IN.)				
No. OF PINS	A	B	C	D
15	1.213	0.984	0.666	0.759
26	1.541	1.312	0.994	1.083
44	2.088	1.852	1.534	1.625



MEETS IP67 STANDARDS

(SEE PAGE 2 FOR SEALING DETAILS)

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 06-11-09		
		CHECKED:		DATE:		
NorComp		SCALE: 1 : 1	SHEET 1		OF 2	REV 3
		DWG NO. 780-MYY-103L YY1				


RoHS COMPLIANT



DETAIL A-A

HARDWARE OPTION

01X 0.065" (BOARD SIDE) - CN1



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-26-09		
		CHECKED:		DATE:		
			SCALE: 2.5 : 1	SHEET 2	OF 2	REV 3
			DWG NO. 780-MYY-103LYY1			