


General ordering data

Order No.	0342600000
Part designation	KLIPPON K7
Version	Housings, 91 mm, 160 mm, 350 mm, Aluminium alloy (AlSi12)
EAN	4008190471392
Qty.	1 pc(s).

Dimensions

Fixing dimension, width	330 mm
Height	91 mm
Length	160 mm
Width	350 mm

General details

Cover fixing	M5 screws, captive
Enclosure fixing	Holes 6 mm
Integral fixing	Threaded holes M5
Resistance to shocks	10 J
Sealing material	Neoprene
Version cover	closed
Surface finish	untreated
Class of protection to EN 60529	IP 66 and IP 67
Weight	2,870 g
Ambient temperature, min.	-30 °C
Ambient temperature, max.	80 °C

Screwed cable glands top/bottom

M 12	42
M 16	26
M 20	17
M 25	10
M 32	6
M 40	5
Side of enclosure	Top / Bottom

Screwed cable glands top/bottom**Screwed cable glands, left/right**

M12	8
M16	6
M20	3
M25	2
M32	2
M40	1
On housing side	left / right

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000058
ETIM 3.0	EC000058
eClass 4.1	27-14-12-06
eClass 5.0	27-14-91-07
eClass 5.1	27-14-91-07

Similar products

Order No.	Part designation	Version
9529260000	KLIPPON K7 RAL7001	Housings, 91 mm, 160 mm, 350 mm, Aluminium alloy (AlSi12)