

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310671010](#)
Status: **Active**
Overview: H-DAC™ 64 Single Row
Description: 2.54mm (.100") H-DAC 64™, 3 Way Receptacle Assembly, Single-Row, Polarization A

Documents:
[Drawing \(PDF\)](#)
[Application Specification \(PDF\)](#)
[Product Specification PS-31067-0001 \(PDF\)](#)
[Product Specification PS-31100-0001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Housings
Series [31067](#)
Comments Polarization Option A, Black
Overview [H-DAC™ 64 Single Row](#)
Product Name H-DAC 64™

Physical
Circuits (maximum) 3
Circuits Detail 3
Color - Resin Black, White
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Modified Polystyrene, Polyester
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface (in) 0.100 In
Pitch - Mating Interface (mm) 2.54 mm
Pitch - Term. Interface (in) 0.100 In
Pitch - Term. Interface (mm) 2.54 mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40°C to +100°C

Electrical
Current - Maximum 11A, 9A

Material Info

Reference - Drawing Numbers
Product Specification PS-31067-0001, PS-31100-0001
Sales Drawing SD-31109-003



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Halogen-Free

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[31067Series](#)

Mates With
[31101](#) H-DAC 64™ Vertical Header

Use With
See Product Spec

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION