



DMM 500K COUNTS (DM-860A) (CALIB)

Industrial 500,000-Count Digital Multimeter (Calibrated)

Cat No: DM-860A-C

UPC No: 783310020691

Description

- True RMS, 5-5/6-digit, 500,000-count display for greater accuracy
- Audible input alert helps avoid damage to meter
- Record max, min, and max-min and data hold
- Crest capture (peak hold) max, min and max-min readings
- Relative offset display mode makes monitoring relative measurement changes simple
- Performs frequency, temperature and capacitance measurements, plus diode and continuity tests
- Measures temperatures up to 1832°F
- Autoranging for convenient operation - and to save you time
- 42-segment analog bar graph display capability makes it easy to view quick changes
- Bright, backlit display is easy to read under any light condition
- RS-232 capable, may be connected to a PC for extended measurement capability with optional interface DMSC-9
- Accessories included: (1) 9V battery, bead temperature probe (400°F/ 204°C max.), test leads, protective boot, carrying case
- Lifetime Limited Warranty

Specifications

- Accessory : (1) 9V battery, bead temperature probe (400°F/ 204°C max.), test leads, protective boot, carrying case
- Application : Performs Resistance, Conductance, Frequency, Duty Cycle, Temperature And Capacitance Measurements, Plus Diode And Continuity Tests
- Battery : 9 V
- Replacement Part : TC-20, Carrying Case (included), TSG-3, Sure-Grip Test Leads
- Standard : CUL Listed
- Temperature Rating : 1832 DEG F
- Type : Industrial 500,000 Count
- Voltage Rating : 9 V