


Mounting Hole



Dimensions: mm (in.)

SPECIFICATIONS

- Rating: 30A max. 12/24VDC
- Insulation Resistance: 500VDC 100MΩ Min.
- Dielectric Strength: 1000VAC 1 min.
- Operating Temperature: -25°C~85°C
- Fuse Type: Blade Fuse
- Terminal Push/Pull Strength: >=9.1Kgf
- RoHS Compliant

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

EPD-200776

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-R367-GR](#)