



- Clamp ties are used to attach a bundle to another surface such as a control panel wall or ceiling using another fastener.
- The design allows for bundling before or after screwing clamp in place.

Part Number:	PLC2S-S10-C0
Product Family:	<i>Pan-Ty</i> ® Clamp Ties - Weather Resistant
Product Line:	Clamp Cable Ties

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Clamp Tie, 7.9", Standard cross section
-------------------	---

Product Type:	Cable Ties
---------------	------------

Material:	Weather Resistant Nylon 6.6
-----------	-----------------------------

Color:	Black
--------	-------

CSA Certified:	Yes
----------------	-----

UL Listed (File #E56854):	No
---------------------------	----

UL Recognized (File #E56854):	Yes
-------------------------------	-----

Length (In.):	7.9
---------------	-----

Length (mm):	201
--------------	-----

Width (In.):	.190
Width (mm):	4.8
Boss Height (In.):	.160
Boss Height (mm):	4.1
Boss Width (In.):	.373
Boss Width (mm):	9.5
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.84
Max. Bundle Diameter (mm):	47
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M5
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Nominal Hole Diameter (In.):	.200
Nominal Hole Diameter (mm):	5.1
Screw Size:	#10

Std. Pkg. UOM:	PK
Thickness (In.):	.047
Thickness (mm):	1.2
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100