


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	08/15/01	MCCORMICK
B	PRODUCT VALIDATION UPDATES [ECN 1204]	12/10/02	MCCORMICK
C	ECN3026: CN RELEASE	10/02/07	D.PARHAM
D	ECN 6519: UPDATED FORMAT, PACKAGING, AND LOGOS	11/19/12	D. DESJARDIN



PART NUMBER	LENGTH FEET [METERS]
CC59B-05	0.5 [.15]
CC59B-1	1.0 [.30]
CC59B-1.5	1.5 [.46]
CC59B-2	2.0 [.61]
CC59B-2.5	2.5 [.76]
CC59B-3	3.0 [.91]
CC59B-4	4.0 [1.22]
CC59B-5	5.0 [1.52]
CC59B-6	6.0 [1.83]
CC59B-7.5	7.5 [2.29]
CC59B-10	10.0 [3.05]
CC59B-12	12.0 [3.66]
CC59B-15	15.0 [4.57]
CC59B-25	25.0 [7.62]
CC59B-50	50.0 [15.24]
CC59B-75	75.0 [22.86]
CC59B-100	100.0 [30.48]
CC59B-150	150.0 [45.72]
CC59B-200	200.0 [60.96]

NOTES:

- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY ENG	DATE 05/03/01 06/06/01 08/15/01	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY AUDIO/VIDEO		PRODUCT DESCRIPTION CA BNC M/BNC M RG59A/U	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE	CAD FILE: CC59B.SLDDRW	DWG. NO. CC59B	REV. D