

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660117](#)
Status: **Active**
Overview: Premo-Flex™ Cable Jumpers
Description: 0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 12 Circuits, 0.03m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

Drawing (PDF)	Packaging Specification PK-98266-001 (PDF)
Product Specification PS-98266-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	98266
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ Cable Jumpers
Product Name	Premo-Flex™ FFC Jumper
UPC	756054767504

Physical

Cable Length	0.03m
Circuits (Loaded)	12
Net Weight	0.134/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001
Product Specification	PS-98266-001
Sales Drawing	SD-98266-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[98266](#) Series

Use With

Molex FFC – FPC connector.
Be sure to match like plating