




| PANDUIT<br>PART NO. * | BUNDLE DIA.     |                 | A             | B             | C             | D             | E              | F             | MIN. LOOP<br>TENSILE lbs.<br>(N) | CROSS<br>SECTION | TIP<br>STYLE | WEIGHT<br>lbs./100 pcs.<br>(g) |
|-----------------------|-----------------|-----------------|---------------|---------------|---------------|---------------|----------------|---------------|----------------------------------|------------------|--------------|--------------------------------|
|                       | MIN. in<br>(mm) | MAX. in<br>(mm) |               |               |               |               |                |               |                                  |                  |              |                                |
| PLT4S                 | .06<br>(1.5)    | 4.00<br>(102)   | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6)  | 14.5<br>(368) | 50<br>(222)                      | STANDARD         | CURVED       | .56<br>(254)                   |
| PLT4.5S               | .06<br>(1.5)    | 4.50<br>(114)   | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6)  | 15.5<br>(394) | 50<br>(222)                      | STANDARD         | CURVED       | .57<br>(257)                   |
| PLT5S                 | .06<br>(1.5)    | 5.00<br>(127)   | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6)  | 17.5<br>(445) | 50<br>(222)                      | STANDARD         | CURVED       | .65<br>(293)                   |
| PLT6LH                | .188<br>(4.8)   | 6.00<br>(152)   | .075<br>(1.9) | .300<br>(7.6) | .350<br>(8.8) | .330<br>(8.4) | .480<br>(12.2) | 21.9<br>(556) | 120<br>(534)                     | LIGHT HEAVY      | STRAIGHT     | 1.86<br>(845)                  |
| PLT7LH                | .188<br>(4.8)   | 7.00<br>(178)   | .075<br>(1.9) | .300<br>(7.6) | .350<br>(8.8) | .330<br>(8.4) | .480<br>(12.2) | 24.7<br>(627) | 120<br>(534)                     | LIGHT HEAVY      | STRAIGHT     | 2.09<br>(950)                  |
| PLT8LH                | .188<br>(4.8)   | 8.00<br>(203)   | .075<br>(1.9) | .300<br>(7.6) | .350<br>(8.8) | .330<br>(8.4) | .480<br>(12.2) | 27.6<br>(701) | 120<br>(534)                     | LIGHT HEAVY      | STRAIGHT     | 2.32<br>(1054)                 |
| PLT9LH                | .188<br>(4.8)   | 9.00<br>(229)   | .075<br>(1.9) | .300<br>(7.6) | .350<br>(8.8) | .330<br>(8.4) | .480<br>(12.2) | 30.5<br>(775) | 120<br>(534)                     | LIGHT HEAVY      | STRAIGHT     | 2.56<br>(1161)                 |
| PLT10LH               | .188<br>(4.8)   | 10.31<br>(262)  | .075<br>(1.9) | .300<br>(7.6) | .350<br>(8.8) | .330<br>(8.4) | .480<br>(12.2) | 34.3<br>(871) | 120<br>(534)                     | LIGHT HEAVY      | STRAIGHT     | 2.83<br>(1285)                 |

**NOTES:**

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- \*2) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

|  |  |  |  |  |  |                                                                    |  |  |  |
|--|--|--|--|--|--|--------------------------------------------------------------------|--|--|--|
|  |  |  |  |  |  | TITLE                                                              |  |  |  |
|  |  |  |  |  |  | PAN-TY CABLE TIES - PLT SERIES                                     |  |  |  |
|  |  |  |  |  |  | CUSTOMER DRAWING                                                   |  |  |  |
|  |  |  |  |  |  | ITEM REVISION NAME                                                 |  |  |  |
|  |  |  |  |  |  | W10001CC/26                                                        |  |  |  |
|  |  |  |  |  |  | DATASET FILE NAME                                                  |  |  |  |
|  |  |  |  |  |  | W10001CC/26-SS-5540 SHEET 3 CUSTOMER                               |  |  |  |
|  |  |  |  |  |  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN (mm) |  |  |  |
|  |  |  |  |  |  | .X : - - - .XXX : .020 (.51)                                       |  |  |  |
|  |  |  |  |  |  | .XX : .02 (.51) ANGLES : - - -                                     |  |  |  |
|  |  |  |  |  |  | THIRD ANGLE<br>PROJECTION                                          |  |  |  |
|  |  |  |  |  |  | DRAWING NUMBER:                                                    |  |  |  |
|  |  |  |  |  |  | SS-5540 SHEET 3                                                    |  |  |  |
|  |  |  |  |  |  | DRAWN BY                                                           |  |  |  |
|  |  |  |  |  |  | CEW                                                                |  |  |  |
|  |  |  |  |  |  | DATE                                                               |  |  |  |
|  |  |  |  |  |  | 12-27-84                                                           |  |  |  |
|  |  |  |  |  |  | CHK                                                                |  |  |  |
|  |  |  |  |  |  | HVP                                                                |  |  |  |
|  |  |  |  |  |  | SCALE                                                              |  |  |  |
|  |  |  |  |  |  | NONE                                                               |  |  |  |
|  |  |  |  |  |  | SIZE                                                               |  |  |  |
|  |  |  |  |  |  | A                                                                  |  |  |  |

|     |         |     |     |      |                       |            |
|-----|---------|-----|-----|------|-----------------------|------------|
| 26  | 8/13/13 | BWG | KJM | RTFI | UPDATED TITLE BORDER. | SS-5540/26 |
| REV | DATE    | BY  | CHK | APR  | DESCRIPTION           | ECN        |

D101000A/16