


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1272	D	Renamed was CFCC-*	JWM	12/19/01	DJC	12/27/01	DJC	12/27/01
1865	E	RoHS ADDED	DCM	10/17/05	JWM	10/18/05	JWM	10/18/05



PART NO.	"A"	"B" REF.	"C" REF.
CFCC-1	9/16 (14.3)	.40 (10.2)	.25 (6.4)
CFCC-2	1-1/16(27.0)	.88 (22.3)	.25 (6.4)

NOTES:

1. MATERIAL: NORYL
2. COLOR: WHITE
3. FLAMMABILITY RATING: UL94V-1
4. CONTINUOUS USE TEMPERATURE:
-40°F(-40°C) TO 181°F(83°C)
5. MOUNTS BY DOUBLE ADHESIVE TAPE.
See tech note TN-003 for instructions



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITHE.

TOLERANCES:
Tolerances: Unless
Otherwise Specified:
.XX = ±.010
.XXX = ±.005
Fractional = ±1/64
Angles = ±1°

DRAWN BY: JC DATE: 2/18/91
CHECKED BY: JC DATE: 2/18/91
APPROVED BY: JC DATE: 2/18/91

DRAWING TITLE: Continuous Flat Cable Clamps
SIZE A DWG. NO. TA-471 ELECTRONIC FILE TA-471.dwg REV E
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1