

*** 2420 SERIES ***

MATERIAL :

INSULATOR: NYLON6/6 RATED UL94V-0

Ordering information:

2420S**00**

1 2

RoHS COMPLIANT

1.No.ofcircuits

2.Base color:

00=WHITE

01=BLACK

02=BROWN

03=RED

04=ORANGE





05=YELLOW

06=GREEN

07=BLUE

08=VIOLET

09=GRAY



2420S1500**	15	35.00(1.378)	39.5(1.555)	37.8(1.488)
2420S1400**	14	32.50(1.280)	37.0(1.457)	35.3(1.390)
2420S1300**	13	30.00(1.181)	34.5(1.358)	32.8(1.291)
2420S1200**	12	27.50(1.083)	32.0(1.260)	30.3(1.193)
2420S1100**	11	25.00(.984)	29.5(1.161)	27.8(1.094)
2420S1000**	10	22.50(.886)	27.0(1.063)	25.3(.996)
2420S0900**	9	20.000(.787)	24.5(.965)	22.80(.898)
2420S0800**	8	17.500(.689)	22.0(.866)	20.30(.799)
2420S0700**	7	15.000(.591)	19.5(.768)	17.80(.701)
2420S0600**	6	12.500(.492)	17.0(.669)	15.30(.602)
2420S0500**	5	10.000(.394)	14.5(.571)	12.80(.504)
2420S0400**	4	7.500(.295)	12.0(.472)	10.30(.406)
2420S0300**	3	5.000(.197)	9.5(.374)	7.80(.307)
2420S0200**	2	2.500(.098)	7.0(.276)	5.30(.209)
PART NO.	CIRCUITS	DIM. A	DIM. B	DIM. C



LEOCO CORPORATION

GENERAL TOLERANCES:
(UNLESS SPECIFIED)

mm inch

1 PLACE ± 0.30 ± --

2 PLACES ± 0.20 ± .012

3 PLACES ± 0.10 ± .008

4 PLACES ± -- ± .004

ANGULAR ± (1°)

APPROVED:


DATE:

CHECKED:

DATE:

DRAWN:

DATE:



UNITS
mm
inch

PART NO.:

2420S**00**

TITLE:

HOUSING

DRAWING NO.:

242002S

SCALE

SIZE

SHEET

REV.

4:1

A4

1/1

D