


AC FANS


Model 148

Size: 172 mm x 38 mm (6.75" x 1.5")




Part Number	Bearings	Voltage(VAC)	Frequency(Hz)	Current(mA)	Input(watts)	Noise(dBA)	Speed(rpm)	Airflow(cfm)
148VK-0282-030	Ball	115	50/60	300/270	32/32	54/57	2850/3300	213/253
148VK-0281-030	Ball	220	50/60	200/170	35/33	53/57	2800/3200	213/249
148VP-0282-030	Ball	115	50/60	120/160	14/18	50/45.5	2350/2100	172/149
148VP-0281-030	Ball	220	50/60	70/100	16/22	49/44	2400/2000	174/149
148VE-0282-030	Ball	115	50/60	100/90	11/11	36/39	1400/1650	104/123
148VE-0281-030	Ball	220	50/60	60/60	13/14	36/39	1400/1650	104/123


148VE Performance Curve



148VP Performance Curve



148VK Performance Curve



ETRI Model 148 AC FANS

Size: 172 mm x 38 mm (6.75" x 1.5")



ELECTRICAL SPECIFICATIONS

Item	Specification	Conditions/Tolerances
Motor type	permanent split capacitor	multi-pole
Rated Voltage	115 VAC or 220 VAC	±10%
Frequency	50/60 Hz.	Able to operate at either frequency
Input Current	At nominal voltage	±10%
Input Power	At nominal voltage	±10%
Max air flow / Back pressure	All tested in submerged orifice chamber	±4% cfm/±8% pressure
Dielectric strength	2250 VAC	5 sec, 4mA leakage
Electrical Connection	"110" Faston terminals	
Speed	At nominal voltage	±4%

MECHANICAL SPECIFICATIONS

Item	Specification	Conditions
Life expectancy	50,000 hours	continuous operation @ 25° C, 65% relative humidity
Bearing	ball bearing	Use under 70°C
Airflow direction	air intake over impeller	
Housing material	Zamak (zinc alloy)	single piece die-cast housing
Impeller	Lexan 500-10% glass filled	UL 94V-0
Weight	1.1 kg (38.7 oz)	
Rotation	clock-wise viewed from impeller	

ENVIRONMENTAL SPECIFICATIONS


Item	Specification	Conditions
Operating temperature	-10 to +70°C	Ball bearing
Storage temperature	-40 to +70°C	6 months max.
Paint	Black enamel	
Acoustical	Anechoic chamber at free air	Microphone - 1 meter away

PROTECTION

Item	Specification	Conditions
Locked rotor	thermal/impedance protected	148VK thermal protection/148VE,148VP impedance protected
Insulation class	UL class A	
Agency approvals	UL, CSA, VDE*, CE	
Warranty	3 years	

*VDE approval available on some models. Consult factory.

PANEL CUT-OUT



ACCESSORIES

ETRI fans are available with a wide range of accessories, from finger guards to filter assemblies to special termination. Request our accessories brochure or call your nearest distributor for complete details.



1503, Rocky River Road North
Monroe, NC 28110 USA
Tel: 704.289.5423
Fax: 704.283.7170

9-11, rue de Moulin des Bruyères
92400 Courbevoie FRANCE
Tel: (33-1) 49 04 92 00
Fax: (33-1) 47 89 09 38

Website: <http://www.etrinet.com> Email: sales@etrinet.com