

12V Flexiprint

High bright (PLCC6)

Specifications

Voltage	12V
Current	3A
Wattage	14.4W/m
Number of LED's	150pcs
Length of Stripe	2.5m
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C
Viewing Angle	110°
CE/UL/RoHS compliant	

Benefits


Adhesive tape on backside
cutable every ~50mm



Electrical and Optical Characteristics (Ta=25°C)

Part Number	Colour	Wavelength	Intensity lm (typ.)
FP3-A02B-250	 amber	605nm	270
FP3-B02B-250	 blue	472nm	145
FP3-G02B-250	 green	525nm	600
FP3-H02B-250	 warm-white	2600-2800°K	2025
FP3-N02B-250	 warm-white	3000-3500°K	2025
FP3-R02B-250	 red	639nm	315
FP3-S02B-250	 natural-white	4000-5000°K	2400
FP3-W02B-250	 white	6000-7000°K	2400
FP3-Y02B-250	 yellow	590nm	270

Dimensions



Thickness: 2.1 mm

1. All dimensions are in millimetres
2. Tolerance is ± 0.25 mm unless otherwise specified
3. Specifications are subject to change without notice

Please also take note of our **General Information for Flexiprint and LED Modules**