

Power-Assisted Compression Tools: #8 to 900 MCM



Battpac® LT BPLT14BSCR/BPLT14BSCRI 14-Ton Battery-Powered Compression Tools



BPLT14BSCR



Creates Hex-style crimp



BPLT14BSCRI

- Reduced weight and more ergonomic design
- New double-speed feature decreases crimp time by doubling jaw speed until it reaches load
- New more powerful Ni-MH battery has 50% more energy and less memory effect than old batteries
- Rotating head allows maximum flexibility for crimping
- Uses Standard T&B Color-Keyed® 15500 Series dies


Specifications

- Installing Range:
 - Up to 900 mcm copper lugs & splices
 - Up to 750 mcm aluminum lugs & splices
 - CHT814-10 to CHT2502-6 copper H-taps
 - 63105 to 63148 aluminum H-taps
- Output Force: 14 tons
- Dimensions (L x W x H): 18 1/4" x 3 1/8" x 10"
- Battery: Ni-MH 14.4V 3.0Ah
- Weight with Battery: 18.1 lbs.

CAT. NO.	DESCRIPTION	PKG. QTY.
BPLT14BSCR	Battpac® LT 14-Ton Compression Tool. Includes carrying case, charger, two-batteries, carry strap	1
BPLT14BSCRI	Same as above, but insulated head	1

13100A 14-Ton Hydraulic Crimping Head

- Rugged design, made to last in field or on bench
- C-yoke provides maximum flexibility for crimping
- Uses standard T&B Color-Keyed® 15500 Series dies
- Operates on 10,000 psi hydraulic pumps



Creates Hex-style crimp



Specifications

- Installing Range:
 - Up to 900 mcm copper lugs & splices
 - Up to 750 mcm aluminum lugs & splices
 - CHT814-10 to CHT2502-6 copper H-taps
 - 63105 to 63148 aluminum H-taps
- Output Force: 14 tons
- Operating Pressure: 10,000 psi nominal
- Dimensions (L x W x H): 11 1/2" x 2 1/2" x 4 1/4"
- Weight without Dies: 10 lbs.

CAT. NO.	DESCRIPTION	PKG. QTY.
13100A	14-ton hydraulic head with steel case	1