

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 2095234

DB-E388 series Speaker



color Black
ABS Housing Material
Pin Terminal


ELECTRICAL SPECIFICATIONS

Model No.	38MS30008	
Power (Nominal)	(w)	0.15
Power (Max.)	(w)	0.2
Frequency	(Hz.)	700 ~ 4000
Resonant Frequency	(Hz.)	1100 ± 150
Impedance	(Ohm)	8
Sound Output at 10 cm 1000 Hz	(dB)	83
Operating Temperature	(°C)	-20 ~ +60


* Value applying at rated voltage

DIMENSIONS

Top View



Side View



all dimensions are in mm

57

DB-E798 series Speaker



color Black
Noryl SEI Housing Material
Pin Terminal


ELECTRICAL SPECIFICATIONS

Model No.	79MS30008	
Power (Nominal)	(w)	0.15
Power (Max.)	(w)	0.2
Frequency	(Hz.)	700 ~ 5000
Resonant Frequency	(Hz.)	1200 ± 15%
Impedance	(Ohm)	8
Sound Output at 10 cm 1000 Hz	(dB)	82
Operating Temperature	(°C)	-20 ~ +60


* Value applying at rated voltage

DIMENSIONS

Top View



Side View



all dimensions are in mm

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied with respect to accuracy, completeness or results is extended and no liability is assumed. DB Products Ltd. reserves the right to make changes in any specification, data or material contained herein.