






AMP		 E13288 Listed
WIRE RANGE		
16-14HD AWG STRANDED		16-14HD AWG STRANDED
 LR7189 Certified		MILITARY P/N AND CLASS
NOT CERTIFIED		NOT APPLICABLE

1 STAMP AMP 16-14HD* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² [2,050-5,180] CIR MILS
STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES

DR 2-1-93
TA BRINKMAN

CHK 2-1-93
DA PATTERSON

APPD 2-1-93
DE MILLER

APPD 2-1-93
JL MECKLEY

PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

33647

PART NO

FINISH
TIN PLATE

0.00254 [L.000100] MIN
THK PER MIL-T-10727

APPLICATION SPEC

WEIGHT

SCALE

SIZE

CAGE CODE

00779

DRAWING NO

G=33647

TERMINAL, RING TONGUE,
HEAVY DUTY, BUDGET

1 OF 1